






DRY CONTACT INPUT TRACK MOUNT RELAY

RIBM01ZNDC

4.00" Track Mount Relay 30 Amp DPDT, Class 2 Dry Contact Input, 120 Vac Power Input













SPECIFICATIONS

Relays & Contact Type: One (1) DPDT Continuous Duty Coil Expected Relay Life: 10 million cycles minimum mechanical

Operating Temperature: -30 to 140° F

Humidity Range: 5 to 95% (noncondensing)

Operate Time: 18ms

Relay Status: Red LED On = Activated Power Status: Green LED On = Activated **Dimensions:** 2.875" x 4.000" x 1.750"

Track Mount: 4.000"

MT4 Mounting Track Sold Separately

Approvals: UL Component Recognized, UL916

C-UL, CE, RoHS

Gold Flash: Yes Override Switch: No

Contact Ratings:

30 Amp Resistive @ 300 Vac 770 VA @ 120 Vac 25 Amp Resistive @ 28 Vdc 1158 VA @ 240 Vac 15 Amp Resistive @ 600 Vac 1109 VA @ 277 Vac 3 HP @ 480-600 Vac 1640 VA @ 480 Vac 2 HP @ 240/277 Vac NEMA B600 Pilot Duty

1 HP @ 120 Vac

20 Amp Ballast @ 277-480 Vac Not rated for Electronic Ballast

Power Input:

95 mA @ 120 Vac

Notes:

• Dry Contact Input Operation: Close dry contact to activate relay.

• If more than one dry contact input RIB shares a single dry contact input, DCI COM must be common.