
10 AMP PILOT CONTROL RELAY

RIBU2S2

Enclosed Relays 10 Amp 2 SPST-N/O + 2 Overrides with 10-30 Vac/dc/120 Vac Coil





SPECIFICATIONS

Relays & Contact Type: Two (2) SPST Continuous Duty Coil Expected Relay Life: 10 million cycles minimum mechanical

Operating Temperature: -30 to 140° F

Humidity Range: 5 to 95% (noncondensing)

Operate Time: 20ms

Relay Status: LED On = Activated

Dimensions: 4.00" x 4.00" x 1.80" with .50" NPT nipple

Wires: 16", 600V Rated

Approvals: UL Listed, UL916, UL864, C-UL

California State Fire Marshal, CE, RoHS

Housing Rating: UL Accepted for Use in Plenum, NEMA 1

Gold Flash: Yes Override Switch: Yes (2)

Contact Ratings:

10 Amp Resistive @ 277 Vac 480 VA Pilot Duty @ 277 Vac 480 VA Ballast @ 277 Vac Not rated for Electronic Ballast 600 Watt Tungsten @ 120 Vac (N/O) 240 Watt Tungsten @ 120 Vac (N/C) 1/3 HP @ 120-240 Vac (N/O) 1/6 HP @ 120-240 Vac (N/C) 1/4 HP @ 277 Vac (N/O) 1/8 HP @ 277 Vac (N/C)

Coil Current:

33 mA @ 10 Vac 35 mA @ 12 Vac 46 mA @ 24 Vac 55 mA @ 30 Vac 28 mA @ 120 Vac 13 mA @ 10 Vdc 15 mA @ 12 Vdc 18 mA @ 24 Vdc 20 mA @ 30 Vdc

Coil Voltage Input:

10-30 Vac/dc; 120 Vac; 50-60 Hz Drop Out = $2.1 \, \text{Vac} / 2.8 \, \text{Vdc}$ Pull In = 9 Vac / 10 Vdc

• Order Normally Closed by adding "-NC" to end of model number