



SECTION 1) IDENTIFICATION

Product ID: PVT Masonry Veneer Mortar HB
Product Name: Cement-based Construction Mortar
Revision Date: Sep 09, 2021 **Date Printed:** Sep 09, 2021
Version: 1.0 **Supersedes Date:** N.A.
Manufacturer's Name: BLUESTONE PRODUCTS, a TCC Materials Company
Address: 2025 CENTRE POINTE BLVD, MENDOTA HEIGHTS, MN, US, 55120
Emergency Phone: 800-424-9300
Information Phone Number: 651-688-9116
Fax:
Product/Recommended Uses:

SECTION 2) HAZARD IDENTIFICATION

Classification

Specific Target Organ Toxicity - Repeated Exposure - Category 2

Pictograms



Signal Word

Warning

Hazardous Statements - Health

H373 - May cause damage to organs through prolonged or repeated exposure.

Precautionary Statements - General

P101 - If medical advice is needed, have product container or label at hand.

P102 - Keep out of reach of children.

P103 - Read label before use.

Precautionary Statements - Prevention

P260 - Do not breathe dust/fume/gas/mist/vapors/spray.

Precautionary Statements - Response

P314 - Get Medical advice/attention if you feel unwell.

Precautionary Statements - Storage

No precautionary statement available.

Precautionary Statements - Disposal

P501 - Dispose of contents/container in accordance with local/national/international regulations.

Hazards Not Otherwise Classified (HNOC)

None.

SECTION 3) COMPOSITION/INFORMATION ON INGREDIENTS

CAS	Chemical Name	% By Weight
0065997-15-1	PORTLAND CEMENT SILICATE	36.25% - 49.05%
0014808-60-7	SILICA, CRYSTALLINE	30.05% - 40.65%

SECTION 4) FIRST-AID MEASURES

Inhalation

Remove source of exposure or move person to fresh air and keep comfortable for breathing.

If exposed/If you feel unwell/If concerned:

Call a POISON CENTER/doctor.

Eye Contact

Gently brush product off face.

Do not rub eyes.

Let the eyes water naturally for a few minutes.

Look right and left, then up and down.

If particle/dust does not come out, cautiously rinse eyes with lukewarm, gently flowing water for 5 minutes or until particle/dust is removed, while holding the eyelids open.

If eye irritation persists:

Get medical advice/attention.

Do not attempt to manually remove anything from the eyes.

Skin Contact

Take off immediately all contaminated clothing, shoes and leather goods (e.g. watchbands, belts).

Wash with plenty of lukewarm, gently flowing water for a duration of 15-20 minutes.

Call a POISON CENTER/doctor if you feel unwell.

Wash contaminated clothing before re-use or discard.

Ingestion

Rinse mouth.

If exposed/If you feel unwell/If concerned:

Call a POISON CENTER/doctor.

Most Important Symptoms and Effects, Both acute and Delayed

No data available.

Indication of Any Immediate Medical Attention and Special Treatment Needed

Contact poison treatment specialist immediately if large quantities have been ingested or inhaled. No specific treatment is required. No action shall be taken involving any personal risk or without suitable training. It may be dangerous to the person providing aid to give mouth-to-mouth resuscitation. Treat symptomatically.

SECTION 5) FIRE-FIGHTING MEASURES

Suitable Extinguishing Media

Small Fire : Dry chemical, foam, carbon dioxide, water-spray or alcohol-resistant foam. Carbon dioxide can displace oxygen. Use caution when applying carbon dioxide in confined spaces. Large Fire : Water spray, fog or alcohol-resistant foam.

Unsuitable Extinguishing Media

Do not use straight stream of water.

Specific Hazards in Case of Fire

Fire will produce irritating gases.

Fire-Fighting Procedures

Isolate immediate hazard area and keep unauthorized personnel out. Stop spill/release if it can be done safely. Move undamaged containers from immediate hazard area if it can be done safely. Cool containers with flooding quantities of water until well after fire is out. Dispose of fire debris and contaminated extinguishing water in accordance with official regulations.

Special Protective Actions

Wear protective pressure self-contained breathing apparatus (SCBA) and full turnout gear.

SECTION 6) ACCIDENTAL RELEASE MEASURES

Emergency Procedure

Evacuate persons not wearing protective equipment from area of spill until clean-up is complete. Ventilate closed spaces before entering. Do not touch damaged containers or spilled materials unless wearing appropriate protective clothing.

Recommended Equipment

Wear chemical protective clothing and positive pressure self-contained breathing apparatus (SCBA).

Personal Precautions

Do not breathe dust. Do not get on skin, eyes or clothing.

Environmental Precautions

Stop spill/release if it can be done safely. Prevent spilled material and water from clean-up/firefighting from entering sewers, storm drains, other unauthorized drainage systems and natural waterways by using sand, earth, or other appropriate barriers.

Methods and Materials for Containment and Cleaning Up

Avoid raising dust. Safely collect powdered material and deposit in sealed containers for disposal. Ventilate and wash area after clean-up is complete

SECTION 7) HANDLING AND STORAGE

General

Wash hands after use. Avoid contact with skin, eye or clothing. Avoid breathing dust. Use good personal hygiene practices. Eating, drinking and smoking in work areas is prohibited. Remove contaminated clothing and protective equipment before entering eating areas. Eyewash stations and showers should be available in areas where this material is used and stored. All containers must be properly labelled.

Ventilation Requirements

Use only with adequate ventilation to control air contaminants to their exposure limits. The use of local ventilation is recommended to control emissions near the source. Report ventilation failures immediately.

Storage Room Requirements

Store in a cool, dry, well ventilated area, away from sources of ignition and incompatibilities. Keep containers securely sealed when not in use. Containers that have been opened must be carefully resealed to prevent leakage. Indoor storage should meet OSHA standards and appropriate fire codes. Empty containers retain residue and may be dangerous.

SECTION 8) EXPOSURE CONTROLS/PERSONAL PROTECTION

Eye Protection

Wear Dust-proof goggles with side shields

Skin Protection

Gloves must be inspected prior to use. Use proper glove removal technique (without touching glove's outer surface) to avoid skin contact with this product. Use of chemical resistant gloves classified under Standard EN374: Protective gloves against chemicals and microorganisms. Examples of preferred glove barrier materials include: Butyl rubber, Polyethylene, Chlorinated polyethylene, Ethyl vinyl alcohol laminate ("EVAL"). Examples of acceptable glove barrier materials include: Viton, Neoprene, Polyvinyl chloride ("PVC" or "vinyl"), Nitrile/butadiene rubber ("nitrile" or "NBR").

Full contact Material: butyl-rubber Minimum layer thickness: 0.3 mm Break through time: 480 min

Material tested: Butoject® (KCL 897 / Aldrich Z677647, Size M).

Splash contact Material: Nitrile rubber Minimum layer thickness: 0.4 mm Break through time: 30 min

Material tested: Camatril® (KCL 730 / Aldrich Z677442, Size M).

Suitability and durability of a glove is dependent on usage, e.g. frequency and duration of contact, chemical resistance of glove material, glove thickness, dexterity. When prolonged or frequently repeated contact may occur, a glove with a protection class of 5 or higher (breakthrough time greater than 240 minutes according to EN 374) is recommended. When only brief contact is expected, a glove with a protection class of 3 or higher (breakthrough time greater than 60 minutes according to EN 374) is recommended. It should be noted that the time to breakthrough for any glove material may be different for different glove manufacturers. Use of gloves approved to relevant

standards made from the following materials may provide suitable chemical protection: PVC, neoprene or nitrile rubber gloves. Suitability and durability of a glove is dependent on usage, e.g. frequency and duration of contact, chemical resistance of glove material, glove thickness, dexterity. Always seek advice from glove suppliers. Contaminated gloves should be replaced. Use of an apron and over-boots of chemically impervious materials such as neoprene or nitrile rubber. Launder soiled clothes or properly disposed of contaminated material, which cannot be decontaminated.

Respiratory Protection

If engineering controls do not maintain airborne concentrations to a level which is adequate to protect worker, a respiratory protection program that meets or is equivalent to OSHA 29 CFR 1910.134 should be followed. Check with respiratory protective equipment suppliers.

Appropriate Engineering Controls

Provide exhaust ventilation or other engineering controls to keep the airborne concentrations of vapors below their respective threshold limit value.

Chemical Name	ACGIH TWA (mg/m3)	ACGIH TWA (ppm)	ACGIH STEL (mg/m3)	ACGIH STEL (ppm)	ACGIH Carcinogen	ACGIH TLV Basis	ACGIH Notations	OSHA TWA (mg/m3)
PORTLAND CEMENT SILICATE	1 (E,R)				A4	Pulm func; resp symptoms; asthma	A4	[15]; [5 (a)]; [50 mppcf];
SILICA, CRYSTALLINE	0.025 (R)				A2	Pulmonary fibrosis; lung cancer	A2	[10 mg/m3 percent SiO2+2 / 250 percent SiO2+5 mppcf]; [30 mg/m3 percent SiO2+2];

Chemical Name	OSHA TWA (ppm)	OSHA STEL (mg/m3)	OSHA STEL (ppm)	OSHA Carcinogen	OSHA Skin designation	OSHA Tables (Z1, Z2, Z3)	NIOSH TWA (mg/m3)	NIOSH TWA (ppm)
PORTLAND CEMENT SILICATE						[1]; [3];	10,5a	
SILICA, CRYSTALLINE	a					[1,3]; [3];	0.05e	

Chemical Name	NIOSH STEL (mg/m3)	NIOSH STEL (ppm)	NIOSH Carcinogen
PORTLAND CEMENT SILICATE			
SILICA, CRYSTALLINE			1

(C) - Ceiling limit, (I) - Inhalable fraction, (R) - Respirable fraction, A2 - Suspected Human Carcinogen, A4 - Not Classifiable as a Human Carcinogen, func - Function, irr - Irritation, pulm - Pulmonary, resp - respiratory, URT - Upper respiratory tract

The information in this Section does not list non-hazardous components that might have relevant OSHA Tables (Z1, Z2, Z3), NIOSH TWA (mg/m3), ACGIH TWA (mg/m3), ACGIH Carcinogen, ACGIH TLV Basis, ACGIH Notations, OSHA TWA (mg/m3) regulatory values, if they are present at less than 1%. Please contact manufacturer for more information.

SECTION 9) PHYSICAL AND CHEMICAL PROPERTIES

Physical and Chemical Properties

% Solids By Weight	N/A
Density	N/A lb/gal
Specific Gravity	N/A
<hr/>	
Appearance	N/A
Coefficient Water/Oil	N/A
Evaporation Rate	N/A
Flammability	N/A
Flash Point	N/A

Freezing Point	N/A
Low Boiling Point	N/A
Lower Explosion Level	N/A
Melting Point	N/A
Odor Description	N/A
pH	N/A
Upper Explosion Level	N/A
Vapor Density	N/A
Viscosity	N/A
Water Solubility	N/A

SECTION 10) STABILITY AND REACTIVITY

Stability

Stable under normal storage and handling conditions.

Conditions To Avoid

Avoid heat, sparks, flame and contact with incompatible materials

Hazardous Reactions/Polymerization

Will not occur.

Incompatible Materials

Strong bases, acids, and oxidizing agents.

Hazardous Decomposition Products

Oxides of carbon.

SECTION 11) TOXICOLOGICAL INFORMATION

Acute Toxicity

Based on available data, the classification criteria are not met.

The Acute Toxicity Estimate (ATE) for an oral exposure to this mixture is >5000 mg/kg body weight

The Acute Toxicity Estimate (ATE) for a dermal exposure to this mixture is >5000 mg/kg body weight

The Acute Toxicity Estimate (ATE) for an inhalation (vapour) exposure to this mixture is >20 mg/l

Aspiration Hazard

Based on available data, the classification criteria are not met.

Carcinogenicity

Based on available data, the classification criteria are not met.

Germ Cell Mutagenicity

Based on available data, the classification criteria are not met.

Reproductive Toxicity

Based on available data, the classification criteria are not met.

Respiratory/Skin Sensitization

Based on available data, the classification criteria are not met.

Serious Eye Damage/Irritation

Based on available data, the classification criteria are not met.

Skin Corrosion/Irritation

Based on available data, the classification criteria are not met.

Specific Target Organ Toxicity - Repeated Exposure

May cause damage to organs through prolonged or repeated exposure.

Specific Target Organ Toxicity - Single Exposure

Based on available data, the classification criteria are not met.

Likely Routes of Exposure

Inhalation, Ingestion, Skin contact, Eye contact

Chronic Exposure

0014808-60-7 SILICA, CRYSTALLINE

Prolonged inhalation of respirable crystalline silica dust can result in lung disease (i.e. silicosis and/or lung cancer). Symptoms include coughing, shortness of breath, wheezing and reduced pulmonary function.

Potential Health Effects - Miscellaneous

0014808-60-7 SILICA, CRYSTALLINE

Is an IARC, NTP or OSHA carcinogen. Repeated overexposure to crystalline silica may lead to x-ray changes and chronic lung disease. Inhalation of high dust concentrations may cause: breathing difficulties, lung injury. WARNING: This chemical is known to the State of California to cause cancer.

SECTION 12) ECOLOGICAL INFORMATION

Toxicity

Based on available data, the classification criteria are not met.

Mobility in Soil

No data available.

Bioaccumulative Potential

No data available.

Persistence and Degradability

No data available.

Other Adverse Effects

No data available.

SECTION 13) DISPOSAL CONSIDERATIONS

Waste Disposal

It is the responsibility of the user of the product to determine at the time of disposal whether the product meets local criteria for hazardous waste. Waste management should be in full compliance with national, state and local laws. Empty Containers retain product residue which may exhibit hazards of material, therefore do not pressurize, cut, glaze, weld or use for any other purposes.

SECTION 14) Transport Information

	U.S. DOT Information	IATA Information
UN number:	Not Regulated	Not Regulated
Proper shipping name:	N/A	N/A
Hazard class:	Not Applicable	Not Applicable
Packaging group:	Not Applicable	Not Applicable
Hazardous substance (RQ):	No Data Available	
Marine Pollutant:	No Data Available	
Note / Special Provision:	No Data Available	No Data Available
Toxic-Inhalation Hazard:	No Data Available	

SECTION 15) REGULATORY INFORMATION

Safety, health and environmental regulations

The product has been evaluated against the following relevant regulations: U.S.A Toxic Substance Control Act (TSCA) California Proposition 65 Superfund Amendments and Reauthorization Act of 1986 Title III (Emergency Planning and Community Right-to-Know Act of 1986) Sections 311 and 312 Superfund Amendments and Reauthorization Act of 1986 Title III (Emergency Planning and Community Right-to-Know Act of 1986) Section 313 Comprehensive Environmental Response, Compensation, and Liability Act of 1980 (CERCLA) Section 103

CAS	Chemical Name	% By Weight	Regulation List
0065997-15-1	PORTLAND CEMENT SILICATE	36.25% - 49.05%	SARA312,TSCA
0014808-60-7	SILICA, CRYSTALLINE	30.05% - 40.65%	SARA312,TSCA,CA_Prop65 - California Proposition 65,CA_Prop65_Type_Toxicity_Cancer - CA_Proposition65_Type_Toxicity_Cancer

The information in this Section does not list non-hazardous components that might have relevant SARA312, TSCA regulatory values, if they are present at less than 1%. Please contact manufacturer for more information.



WARNING: This product can expose you to chemicals including SILICA, CRYSTALLINE, which is [are] known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov.

SECTION 16) OTHER INFORMATION

Glossary

ACGIH - American Conference of Governmental Industrial Hygienists; CAS - Chemical Abstracts Service ; Chemtrec - Chemical Transportation Emergency Center; DSL - Domestic Substances List; ESL- Effects screening levels; GHS - "Globally Harmonized System of Classification and Labelling of Chemicals" developed by the United Nations; HMIS - Hazardous Material Information Service; IATA - Dangerous Goods Regulations (DGR) for the air transport (IATA); IMDG - International Maritime Dangerous Goods Code; LC - Lethal Concentration; LD - Lethal Dose; NFPA - National Fire Protection Association; OEL - Occupational Exposure Limits; OSHA- Occupational Safety and Health Administration, US Department of Labor; PEL - Permissible Exposure Limit; SARA 313 - Superfund Amendments and Reauthorization Act, Section 313; SCBA - Self Contained Breathing Apparatus; ppm - parts per million; STEL - Short-term exposure limit; TLV - Threshold Limit Value; TSCA - Toxic Substances Control Act Public Law 94-469; TWA - Time-weighted average; US DOT- US Department of Transportation.

Version 1.0:

Revision Date: Sep 09, 2021

First Edition.

DISCLAIMER

To the best of our knowledge, the information contained herein is accurate. However, neither the above named supplier nor any of its subsidiaries assumes any liability whatsoever for the accuracy or completeness of the information contained herein. Final determination of suitability of any material is the sole responsibility of the user. All materials may present unknown hazards and should be used with caution. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that exist. The above information pertains to this product as currently formulated and is based on the information available at this time. Addition of reducers or other additives to this product may substantially alter the composition and hazards of the product. Since conditions of use are outside our control, we make no warranties, express or implied, and assume no liability in connection with any use of this information.