



SAFETY DATA SHEET

Form Release Oil

SECTION 1) IDENTIFICATION

Product ID: Form Release Oil
Product Name: Concrete form release aid
Revision Date: Dec 16, 2021 **Date Printed:** Mar 16, 2022
Version: 1.0 **Supersedes Date:** N.A.
Manufacturer's Name: BLUESTONE PRODUCTS, a TCC Materials Company
Address: 2025 CENTRE POINTE BLVD, MENDOTA HEIGHTS, MN, US, 55120
Emergency Phone: 800-424-9300
Information Phone Number: 651-688-9116
Fax:
Product/Recommended Uses:

SECTION 2) HAZARDS IDENTIFICATION

Classification

Skin Irritation - Category 3

Pictograms

None

Signal Word

Warning

Hazardous Statements - Health

H316 - Causes mild skin irritation

Precautionary Statements - General

P101 - If medical advice is needed, have product container or label at hand.

P102 - Keep out of reach of children.

P103 - Read label before use.

Precautionary Statements - Prevention

No precautionary statement available.

Precautionary Statements - Response

P332 + P313 - If skin irritation occurs: Get medical advice/attention.

Precautionary Statements - Storage

No precautionary statement available.

Precautionary Statements - Disposal

No precautionary statement available.

Hazards Not Otherwise Classified (HNOC)

None.

Acute toxicity of less than one percent of the mixture is unknown

SECTION 3) COMPOSITION/INFORMATION ON INGREDIENTS

CAS	Chemical Name	GHS Classifications	% By Weight
0007732-18-5	WATER	N.A.	80.00% - 100.00%
0008001-22-7	SOYBEAN OIL	N.A.	0.00% - 5.00%
0000143-28-2	CIS-9-OCTADECEN-1-OL	Eye Irr. 2A, H319; Skin Irr. 2, H315	0.00% - 1.00%
0000112-53-8	1-DODECANOL	Acute Tox. Oral 5, H303; Aquatic Acute 1, H400; Aquatic Chronic 1, H410; Eye Irr. 2A, H319; Skin Irr. 2, H315	Trace

SECTION 4) FIRST-AID MEASURES

Inhalation

Remove source of exposure or move person to fresh air and keep comfortable for breathing.

Call a POISON CENTER/doctor if you feel unwell.

Eye Contact

If irritation occurs, cautiously rinse eyes with lukewarm, gently flowing water for 5 minutes, while holding the eyelids open.

If eye irritation persists:

Get medical advice/attention.

Skin Contact

Rinse/wash with lukewarm, gently flowing water and mild soap for 5 minutes or until product is removed.

If skin irritation occurs or you feel unwell:

Get medical advice/attention.

Wash contaminated clothing before reuse.

Ingestion

Rinse mouth.

If you feel unwell/If concerned:

Get medical advice/attention.

Most important symptoms and effects, both acute and delayed

No data available.

Indication of any immediate medical attention and special treatment needed

Treatment should be supportive and based on the judgement of the physician in response to the reaction of the patient. Treat symptomatically. Contact poison treatment specialist immediately if large quantities have been ingested or inhaled. No specific treatment is required. No action shall be taken involving any personal risk or without suitable training. It may be dangerous to the person providing aid to give mouth-to-mouth resuscitation. Treat according to symptoms (decontamination, vital functions), no known specific antidote.

SECTION 5) FIRE-FIGHTING MEASURES

Suitable Extinguishing Media

Small Fire : Dry chemical, foam, carbon dioxide, water-spray or alcohol-resistant foam. Carbon dioxide can displace oxygen. Use caution when applying carbon dioxide in confined spaces. Large Fire : Water spray, fog or alcohol-resistant foam.

Unsuitable Extinguishing Media

Do not use straight stream of water.

Specific Hazards in Case of Fire

Fire will produce irritating gases.

Fire-fighting Procedures

Isolate immediate hazard area and keep unauthorized personnel out. Stop spill/release if it can be done safely. Move undamaged containers from immediate hazard area if it can be done safely. Cool containers with flooding quantities of water until well after fire is out. Caution should be exercised when using water or foam as frothing may occur, especially if sprayed into containers of hot, burning liquid. Dispose of fire debris and contaminated extinguishing water in accordance with official regulations.

Special Protective Actions

Wear protective pressure self-contained breathing apparatus (SCBA) and full turnout gear.

SECTION 6) ACCIDENTAL RELEASE MEASURES

Emergency Procedure

Isolate hazard area and keep unauthorized personnel away. Stay uphill and/or upstream. Ventilate closed spaces before entering. Do not touch damaged containers or spilled materials unless wearing appropriate protective clothing.

Recommended Equipment

Wear chemical protective clothing.

Personal Precautions

Avoid breathing vapor or mist. Avoid contact with skin, eye or clothing.

Environmental Precautions

Stop spill/release if it can be done safely. Prevent spilled material from entering sewers, storm drains, other unauthorized drainage systems and natural waterways by using sand, earth, or other appropriate barriers.

Methods and Materials for Containment and Cleaning up

Absorb Liquids in vermiculite, dry sand, earth, or similar inert material and deposit in sealed containers for disposal. Ventilate area after clean-up is complete.

SECTION 7) HANDLING AND STORAGE

General

Wash hands after use. Avoid contact with skin, eye or clothing. Avoid breathing vapor or mist. Use good personal hygiene practices. Eating, drinking and smoking in work areas is prohibited. Remove contaminated clothing and protective equipment before entering eating areas. Eyewash stations and showers should be available in areas where this material is used and stored. All containers must be properly labelled.

Ventilation Requirements

Use only with adequate ventilation to control air contaminants to their exposure limits. The use of local ventilation is recommended to control emissions near the source. Report ventilation failures immediately.

Storage Room Requirements

Store in a cool, dry, well ventilated area, away from sources of ignition and incompatibilities. Keep containers securely sealed when not in use. Containers that have been opened must be carefully resealed to prevent leakage. Indoor storage should meet OSHA standards and appropriate fire codes. Empty containers retain residue and may be dangerous.

SECTION 8) EXPOSURE CONTROLS/PERSONAL PROTECTION

Eye protection

Wear eye protection with side shields or goggles. Wear indirect-vent, impact and splash resistant goggles when working with liquids.

Skin Protection

Gloves must be inspected prior to use. Use proper glove removal technique (without touching glove's outer surface) to avoid skin contact with this product. Use of chemical resistant gloves classified under Standard EN374: Protective gloves against chemicals and microorganisms. Examples of preferred glove barrier materials include: Butyl rubber, Polyethylene, Chlorinated polyethylene, Ethyl vinyl alcohol laminate ("EVAL"). Examples of acceptable glove barrier materials include: Viton, Neoprene, Polyvinyl chloride ("PVC" or "vinyl"), Nitrile/butadiene rubber ("nitrile" or "NBR").

Full contact Material: butyl-rubber Minimum layer thickness: 0.3 mm Break through time: 480 min

Material tested: Butoject® (KCL 897 / Aldrich Z677647, Size M).

Splash contact Material: Nitrile rubber Minimum layer thickness: 0.4 mm Break through time: 30 min

Material tested: Camatril® (KCL 730 / Aldrich Z677442, Size M).

Suitability and durability of a glove is dependent on usage, e.g. frequency and duration of contact, chemical resistance of glove material, glove thickness, dexterity. When prolonged or frequently repeated contact may occur, a glove with a protection class of 5 or higher (breakthrough time greater than 240 minutes according to EN 374) is recommended. When only brief contact is expected, a glove with a protection class of 3 or higher (breakthrough time greater than 60 minutes according to EN 374) is recommended. It should be noted that the time to breakthrough for any glove material may be different for different glove manufacturers. Use of gloves approved to relevant standards made from the following materials may provide suitable chemical protection: PVC, neoprene or nitrile rubber gloves. Suitability and durability of a glove is dependent on usage, e.g. frequency and duration of contact, chemical resistance of glove material, glove

thickness, dexterity. Always seek advice from glove suppliers. Contaminated gloves should be replaced. Use of an apron and over-boots of chemically impervious materials such as neoprene or nitrile rubber. Launder soiled clothes or properly disposed of contaminated material, which cannot be decontaminated.

Respiratory protection

If engineering controls do not maintain airborne concentrations to a level which is adequate to protect worker, a respiratory protection program that meets or is equivalent to OSHA 29 CFR 1910.134 should be followed. Check with respiratory protective equipment suppliers.

Appropriate Engineering Controls

Provide exhaust ventilation or other engineering controls to keep the airborne concentrations of vapors below their respective threshold limit value.

Chemical Name	ACGIH TWA (mg/m3)	ACGIH TWA (ppm)	ACGIH STEL (mg/m3)	ACGIH STEL (ppm)	ACGIH Carcinogen	ACGIH TLV Basis	ACGIH Notations	OSHA TWA (mg/m3)
---------------	-------------------	-----------------	--------------------	------------------	------------------	-----------------	-----------------	------------------

Chemical Name	OSHA TWA (ppm)	OSHA STEL (mg/m3)	OSHA STEL (ppm)	OSHA Carcinogen	OSHA Skin designation	OSHA Tables (Z1, Z2, Z3)	NIOSH TWA (mg/m3)	NIOSH TWA (ppm)
---------------	----------------	-------------------	-----------------	-----------------	-----------------------	--------------------------	-------------------	-----------------

Chemical Name	NIOSH STEL (mg/m3)	NIOSH STEL (ppm)	NIOSH Carcinogen
---------------	--------------------	------------------	------------------

(IFV) - Inhalable fraction and vapor, A4 - Not Classifiable as a Human Carcinogen, DSEN - Dermal sensitization, irr - Irritation, sens - sensitization

The information in this Section does not list non-hazardous components that might have relevant NIOSH STEL (mg/m3), NIOSH STEL (ppm), OSHA TWA (ppm), OSHA Tables (Z1, Z2, Z3), NIOSH TWA (mg/m3), NIOSH TWA (ppm), ACGIH TWA (mg/m3), ACGIH TWA (ppm), ACGIH STEL (ppm), ACGIH Carcinogen, ACGIH TLV Basis, ACGIH Notations, OSHA TWA (mg/m3) regulatory values, if they are present at less than 1%. Please contact manufacturer for more information.

SECTION 9) PHYSICAL AND CHEMICAL PROPERTIES

Physical and Chemical Properties

Density	8.29609 lb/gal
Specific Gravity	0.99409
% Solids By Weight	3.84370%

Appearance	N/A
Odor Description	N/A
pH	N/A
Water Solubility	N/A
Flammability	N/A
Flash Point	N/A
Viscosity	N/A
Lower Explosion Level	N/A
Upper Explosion Level	N/A
Vapor Density	N/A
Freezing Point	N/A
Melting Point	N/A
Low Boiling Point	N/A
Evaporation Rate	N/A
Coefficient Water/Oil	N/A

SECTION 10) STABILITY AND REACTIVITY

Stability

Stable under normal storage and handling conditions.

Conditions To Avoid

Avoid heat, sparks, flame and contact with incompatible materials

Hazardous Reactions/Polymerization

Will not occur.

Incompatible Materials

Strong bases, acids, and oxidizing agents.

Hazardous Decomposition Products

Oxides of carbon.

SECTION 11) TOXICOLOGICAL INFORMATION

Acute Toxicity

Based on available data, the classification criteria are not met.

The Acute Toxicity Estimate (ATE) for an oral exposure to this mixture is >5000 mg/kg body weight

The Acute Toxicity Estimate (ATE) for a dermal exposure to this mixture is >5000 mg/kg body weight

The Acute Toxicity Estimate (ATE) for an inhalation (vapour) exposure to this mixture is >20 mg/l

Aspiration Hazard

Based on available data, the classification criteria are not met.

Carcinogenicity

Based on available data, the classification criteria are not met.

Germ Cell Mutagenicity

Based on available data, the classification criteria are not met.

Reproductive Toxicity

Based on available data, the classification criteria are not met.

Respiratory/Skin Sensitization

Based on available data, the classification criteria are not met.

Serious Eye Damage/Irritation

Based on available data, the classification criteria are not met.

Skin Corrosion/Irritation

Causes mild skin irritation

Specific Target Organ Toxicity - Repeated Exposure

Based on available data, the classification criteria are not met.

Specific Target Organ Toxicity - Single Exposure

Based on available data, the classification criteria are not met.

Likely Routes of Exposure

Inhalation, Ingestion, Skin contact, Eye contact

SECTION 12) ECOLOGICAL INFORMATION

Toxicity

Based on available data, the classification criteria are not met.

Persistence and Degradability

No data available.

Bioaccumulative Potential

No data available.

Mobility in Soil

No data available.

Other Adverse Effects

No data available.

SECTION 13) DISPOSAL CONSIDERATIONS

Waste Disposal

It is the responsibility of the user of the product to determine at the time of disposal whether the product meets local criteria for hazardous waste. Waste management should be in full compliance with national, state and local laws. Empty Containers retain product residue which may exhibit hazards of material, therefore do not pressurize, cut, glaze, weld or use for any other purposes.

SECTION 14) TRANSPORT INFORMATION

	U.S. DOT Information	IMDG Information	IATA Information
UN Number:1866 Resin solution	Not Regulated	Not Regulated	Not Regulated
Proper shipping name:	N/A	N/A	N/A
Hazard Class:	Not Applicable	Not Applicable	Not Applicable
Packaging:	Not Applicable	Not Applicable	Not Applicable
Hazardous substance (RQ):	No Data Available		
Marine Pollutant:	No Data Available	No Data Available	
Note / Special Provision:	No Data Available	No Data Available	No Data Available
Toxic-Inhalation Hazard:	No Data Available		

SECTION 15) REGULATORY INFORMATION

Safety, health and environmental regulations

The product has been evaluated against the following relevant regulations: U.S.A Toxic Substance Control Act (TSCA) California Proposition 65 Superfund Amendments and Reauthorization Act of 1986 Title III (Emergency Planning and Community Right-to-Know Act of 1986) Sections 311 and 312 Superfund Amendments and Reauthorization Act of 1986 Title III (Emergency Planning and Community Right-to-Know Act of 1986) Section 313 Comprehensive Environmental Response, Compensation, and Liability Act of 1980 (CERCLA) Section 103

CAS	Chemical Name	% By Weight	Regulation List
0007732-18-5	WATER	80.00% - 100.00%	TSCA
0008001-22-7	SOYBEAN OIL	0.00% - 5.00%	SARA312,TSCA
0000143-28-2	CIS-9-OCTADECEN-1-OL	0.00% - 1.00%	SARA312,TSCA
0004080-31-3	1-(3-CHLOROALLYL)-3,5,7-TRIAZA-1-AZONIAADAMANTANE CHLORIDE	Trace	SARA313, SARA312,TSCA
0000112-53-8	1-DODECANOL	Trace	SARA312,TSCA

The information in this Section does not list non-hazardous components that might have relevant SARA312, TSCA regulatory values, if they are present at less than 1%. Please contact manufacturer for more information.

SECTION 16) OTHER INFORMATION

Glossary

ACGIH - American Conference of Governmental Industrial Hygienists; CAS - Chemical Abstracts Service ; Chemtrec - Chemical Transportation Emergency Center; DSL - Domestic Substances List; ESL - Effects screening levels; GHS - "Globally Harmonized System of Classification and Labelling of Chemicals" developed by the United Nations; HMIS - Hazardous Material Information Service; IATA - Dangerous Goods Regulations (DGR) for the air transport (IATA); IMDG - International Maritime Dangerous Goods Code; LC - Lethal Concentration; LD - Lethal Dose; NFPA - National Fire Protection Association; OEL - Occupational Exposure Limits; OSHA- Occupational Safety and Health Administration, US Department of Labor; PEL - Permissible Exposure Limit; SARA 313 - Superfund Amendments and Reauthorization Act, Section 313; SCBA - Self Contained Breathing Apparatus; ppm - parts per million; STEL - Short-term exposure limit; TLV - Threshold Limit Value; TSCA - Toxic Substances Control Act Public Law 94-469; TWA - Time-weighted average; US DOT- US Department of Transportation.

Version 1.0:

Revision Date: Dec 16, 2021

First Edition.

Full text of H-Statements referred to under Section 3

H319 Causes serious eye irritation
H315 Causes skin irritation
H303 May be harmful if swallowed
H400 Very toxic to aquatic life
H410 Very toxic to aquatic life with long lasting effects

DISCLAIMER

To the best of our knowledge, the information contained herein is accurate. However, neither the above named supplier nor any of its subsidiaries assumes any liability whatsoever for the accuracy or completeness of the information contained herein. Final determination of suitability of any material is the sole responsibility of the user. All materials may present unknown hazards and should be used with caution. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that exist. The above information pertains to this product as currently formulated, and is based on the information available at this time. Addition of reducers or other additives to this product may substantially alter the composition and hazards of the product. Since conditions of use are outside our control, we make no warranties, express or implied, and assume no liability in connection with any use of this information.