



# SAFETY DATA SHEET

Issue Date 06-Oct-2021

Revision Date 06-Oct-2021

Version 1

## 1. PRODUCT AND COMPANY IDENTIFICATION

### Product identifier

**Product Name** Swipe-It!

### Other means of identification

**Product Code** NL212  
**Synonyms** None

### Details of the supplier of the safety data sheet

**Company Name** Nyco Products Company  
5332 Dansher Road,  
Countryside, IL 60525  
(708) 579-8100  
nycoproducts.com

### Emergency telephone number

**Emergency Telephone** Chemtrec 1-800-424-9300

## 2. HAZARDS IDENTIFICATION

### Classification

#### **OSHA Regulatory Status**

This product has been classified in accordance with the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Acute toxicity - Oral	Not classified
Acute toxicity - Dermal	Not classified

### Label elements

#### **Emergency Overview**

**Appearance** Clear Blue

**Physical state** Liquid

**Odor** Almond

#### **Precautionary Statements - Response**

Specific Treatment (See Section 4 on the SDS)

IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing

Call a POISON CENTER or doctor/physician if you feel unwell

IF SWALLOWED: Rinse mouth. DO NOT induce vomiting

Drink plenty of water

Immediately call a POISON CENTER or doctor/physician

#### **Precautionary Statements - Disposal**

Disposal should be in accordance with applicable regional, national and local laws and regulations

### Hazards not otherwise classified (HNOC)

#### Other Information

- Harmful to aquatic life with long lasting effects

Unknown Acute Toxicity

0% of the mixture consists of ingredient(s) of unknown toxicity

### 3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical Name	CAS No.	Weight-%	Trade Secret
2-(2-butoxyethoxy)ethanol	112-34-5	1-5	*

\*The exact percentage (concentration) of composition has been withheld as a trade secret.

### 4. FIRST AID MEASURES

#### First aid measures

<b>Skin Contact</b>	Wash off immediately with soap and plenty of water. If skin irritation persists, call a physician.
<b>Eye contact</b>	Rinse thoroughly with plenty of water for at least 15 minutes, lifting lower and upper eyelids. Consult a physician.
<b>Inhalation</b>	Remove to fresh air.
<b>Ingestion</b>	Clean mouth with water and drink afterwards plenty of water.

#### Most important symptoms and effects, both acute and delayed

**Symptoms** Any additional important symptoms and effects are described in Section 11: Toxicology Information.

#### Indication of any immediate medical attention and special treatment needed

**Note to physicians** Treat symptomatically.

### 5. FIRE-FIGHTING MEASURES

#### Suitable extinguishing media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

**Unsuitable extinguishing media** Caution: Use of water spray when fighting fire may be inefficient.

#### Specific hazards arising from the chemical

No Information available.

#### Explosion data

**Sensitivity to Mechanical Impact** None.

**Sensitivity to Static Discharge** None.

#### Protective equipment and precautions for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

### 6. ACCIDENTAL RELEASE MEASURES

#### Personal precautions, protective equipment and emergency procedures

**Personal precautions** Ensure adequate ventilation, especially in confined areas.

#### Environmental precautions

**Environmental precautions** Do not allow into any storm sewer drains, lakes, streams, ponds, estuaries, oceans or other surface water bodies. Should not be released into the environment. Dispose of according to

all local city, state and federal rules and regulations.

#### Methods and material for containment and cleaning up

**Methods for containment** Prevent further leakage or spillage if safe to do so.

**Methods for cleaning up** Pick up and transfer to properly labeled containers.

### 7. HANDLING AND STORAGE

#### Precautions for safe handling

**Advice on safe handling** Handle in accordance with good industrial hygiene and safety practice.

#### Conditions for safe storage, including any incompatibilities

**Storage Conditions** Keep containers tightly closed in a dry, cool and well-ventilated place.

**Incompatible materials** None known based on information supplied.

### 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

#### Control parameters

#### Exposure Guidelines

Chemical Name	ACGIH TLV	OSHA PEL	NIOSH IDLH
2-(2-butoxyethoxy)ethanol 112-34-5	TWA: 10 ppm inhalable fraction and vapor	-	-

#### Appropriate engineering controls

**Engineering Controls** Showers, Eyewash stations & Ventilation systems.

#### Individual protection measures, such as personal protective equipment

**Eye/face protection** Wear safety glasses with side shields (or goggles).

**Skin and body protection** Rubber gloves if prolonged contact and/or handling large volumes.

**Respiratory protection** Ensure adequate ventilation, especially in confined areas. In case of insufficient ventilation, wear suitable respiratory equipment. If irritation is experienced, move to a well ventilated area.

**General Hygiene** Wear suitable gloves and eye/face protection.

### 9. PHYSICAL AND CHEMICAL PROPERTIES

#### Information on basic physical and chemical properties

**Physical state** Liquid  
**Appearance** Clear Blue  
**Color** Blue  
**Odor** Almond  
**Odor threshold** No Information available

<u>Property</u>	<u>Values</u>	<u>Remarks • Method</u>
pH	10.0 - 12.0	
Specific Gravity	1.002	
Viscosity	< 25 cP @ 25°C	
Melting point/freezing point	No Information available	
Flash point	above 200F	
Boiling point / boiling range	100 °C / 212 °F Degrees	
Evaporation rate	No Information available	
Flammability (solid, gas)	No data available	

<b>Flammability Limits in Air</b>	
<b>Upper flammability limit:</b>	No Information available
<b>Lower flammability limit:</b>	No Information available
<b>Vapor pressure</b>	No Information available
<b>Vapor density</b>	No Information available
<b>Water solubility</b>	Complete
<b>Partition coefficient</b>	No Information available
<b>Autoignition temperature</b>	No Information available
<b>Decomposition temperature</b>	No Information available

**Other Information**

<b>Density Lbs/Gal</b>	8.35
<b>VOC Content (%)</b>	1.5

## 10. STABILITY AND REACTIVITY

**Reactivity**

No data available

**Chemical stability**

Stable under recommended storage conditions.

**Possibility of Hazardous Reactions**

None under normal processing.

**Conditions to avoid**

Extremes of temperature and direct sunlight.

**Incompatible materials**

None known based on information supplied.

**Hazardous Decomposition Products**

None known based on information supplied.

## 11. TOXICOLOGICAL INFORMATION

**Information on likely routes of exposure****Product Information**

<b>Inhalation</b>	Avoid breathing vapors or mists. Inhalation of vapors in high concentration may cause irritation of respiratory system.
<b>Eye contact</b>	Avoid contact with eyes. Contact with eyes may cause irritation or burns.
<b>Skin Contact</b>	Avoid contact with skin. Prolonged contact may cause redness and irritation.
<b>Ingestion</b>	Do not taste or swallow. Can burn mouth, throat, and stomach. May cause gastro intestinal irritation.

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
2-(2-butoxyethoxy)ethanol 112-34-5	= 5660 mg/kg ( Rat )	= 2700 mg/kg ( Rabbit )	-

**Information on toxicological effects****Symptoms** No Information available.**Delayed and immediate effects as well as chronic effects from short and long-term exposure**

**Sensitization** No Information available.  
**Germ cell mutagenicity** No Information available.

<b>Carcinogenicity</b>	No Information available.
<b>Reproductive toxicity</b>	No Information available.
<b>STOT - single exposure</b>	No Information available.
<b>STOT - repeated exposure</b>	No Information available.
<b>Aspiration hazard</b>	No Information available.

**Numerical measures of toxicity - Product Information**

**Unknown Acute Toxicity** 0% of the mixture consists of ingredient(s) of unknown toxicity

**12. ECOLOGICAL INFORMATION****Ecotoxicity**

0% of the mixture consists of components(s) of unknown hazards to the aquatic environment

<b>Chemical Name</b>	<b>Algae/aquatic plants</b>	<b>Fish</b>	<b>Crustacea</b>
2-(2-butoxyethoxy)ethanol 112-34-5	100: 96 h Desmodesmus subspicatus mg/L EC50	1300: 96 h Lepomis macrochirus mg/L LC50 static	100: 48 h Daphnia magna mg/L EC50
PROPRIETARY	-	1.2: 96 h Oncorhynchus mykiss mg/L LC50	5.3: 48 h Daphnia mg/L LC50
Alanine, N,N-bis(carboxymethyl)-, trisodium salt 164462-16-2	-	110: 96 h Danio rerio mg/L LC50 static	-

**Persistence and degradability**

No Information available.

**Bioaccumulation**

No Information available.

**Other adverse effects**

No Information available

**13. DISPOSAL CONSIDERATIONS****Waste treatment methods****Disposal of wastes**

Disposal should be in accordance with applicable regional, national and local laws and regulations.

**Contaminated packaging**

Do not reuse container.

**14. TRANSPORT INFORMATION**

The basic description below is specific to the container size. This information is provided for at a glance DOT information. Please refer to the container and/or shipping papers for the appropriate shipping description before tendering this material for shipment. For additional information, please contact the distributor listed in section 1 of this SDS.

**DOT** Not regulated

**TDG** Not regulated

**15. REGULATORY INFORMATION****International Inventories**

**TSCA** Complies  
**DSL/NDL** Complies

**Legend:**

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

**US Federal Regulations****SARA 313**

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product contains a chemical or chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

Chemical Name	SARA 313 - Threshold Values %
2-(2-butoxyethoxy)ethanol - 112-34-5	1.0

**SARA 311/312 Hazard Categories**

Acute health hazard	No
Chronic Health Hazard	No
Fire hazard	No
Sudden release of pressure hazard	No
Reactive Hazard	No

**CWA (Clean Water Act)**

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

**CERCLA**

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material

**US State Regulations****California Proposition 65**

This product has been evaluated and does not require warning labeling under California Proposition 65.

**U.S. State Right-to-Know Regulations**

Chemical Name	New Jersey	Massachusetts	Pennsylvania
2-(2-butoxyethoxy)ethanol 112-34-5	X	-	X

**U.S. EPA Label Information**

EPA Pesticide Registration Number Not Applicable

**16. OTHER INFORMATION**

<b>NFPA</b>	Health hazards 1	Flammability 0	Instability 0	Physical and Chemical Properties -
<b>HMIS</b>	Health hazards 1	Flammability 0	Physical hazards 0	Personal protection B

Issue Date 06-Oct-2021

Revision Date 06-Oct-2021

**Revision Note**

No Information available

**Disclaimer**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other

materials or in any process, unless specified in the text.

**End of Safety Data Sheet**