



SAFETY DATA SHEET

Issue Date 02-Aug-2021

Revision Date 02-Aug-2021

Version 1

1. PRODUCT AND COMPANY IDENTIFICATION

Product identifier

Product Name Pet Stain Remover

Other means of identification

Product Code NL90390

Synonyms None

Details of the supplier of the safety data sheet

Company Name Nyco Products Company
5332 Dansher Road,
Countryside, IL 60525
(708) 579-8100
nycoproducts.com

Emergency telephone number

Emergency Telephone Chemtrec 1-800-424-9300

2. HAZARDS IDENTIFICATION

Classification

OSHA Regulatory Status

This product has been classified in accordance with the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Label elements

Emergency Overview

Appearance Slightly Opaque

Physical state Liquid

Odor Fresh & Clean

Precautionary Statements - Response

Specific Treatment (See Section 4 on the SDS)

IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing

Call a POISON CENTER or doctor/physician if you feel unwell

IF SWALLOWED: Rinse mouth. DO NOT induce vomiting

Drink plenty of water

Immediately call a POISON CENTER or doctor/physician

Precautionary Statements - Disposal

Disposal should be in accordance with applicable regional, national and local laws and regulations

Hazards not otherwise classified (HNOC)

Other Information

Unknown Acute Toxicity

2.0105501% of the mixture consists of ingredient(s) of unknown toxicity

3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical Name	CAS No.	Weight-%	Trade Secret
Viable Bacterial Cultures	Proprietary	1-5	*

*The exact percentage (concentration) of composition has been withheld as a trade secret.

4. FIRST AID MEASURES

First aid measures

Skin Contact	Wash off immediately with soap and plenty of water. If skin irritation persists, call a physician.
Eye contact	Rinse thoroughly with plenty of water for at least 15 minutes, lifting lower and upper eyelids. Consult a physician.
Inhalation	Remove to fresh air.
Ingestion	Clean mouth with water and drink afterwards plenty of water.

Most important symptoms and effects, both acute and delayed

Symptoms	Any additional important symptoms and effects are described in Section 11: Toxicology Information.
-----------------	--

Indication of any immediate medical attention and special treatment needed

Note to physicians	Treat symptomatically.
---------------------------	------------------------

5. FIRE-FIGHTING MEASURES

Suitable extinguishing media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable extinguishing media Caution: Use of water spray when fighting fire may be inefficient.

Specific hazards arising from the chemical

No Information available.

Explosion data

Sensitivity to Mechanical Impact None.

Sensitivity to Static Discharge None.

Protective equipment and precautions for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal precautions	Ensure adequate ventilation, especially in confined areas.
-----------------------------	--

Environmental precautions

Environmental precautions	Do not allow into any storm sewer drains, lakes, streams, ponds, estuaries, oceans or other surface water bodies. Should not be released into the environment. Dispose of according to all local city, state and federal rules and regulations.
----------------------------------	---

Methods and material for containment and cleaning up

Methods for containment Prevent further leakage or spillage if safe to do so.

Methods for cleaning up Pick up and transfer to properly labeled containers.

7. HANDLING AND STORAGE

Precautions for safe handling

Advice on safe handling Handle in accordance with good industrial hygiene and safety practice.

Conditions for safe storage, including any incompatibilities

Storage Conditions Keep containers tightly closed in a dry, cool and well-ventilated place.

Incompatible materials None known based on information supplied.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

Exposure Guidelines

Chemical Name	ACGIH TLV	OSHA PEL	NIOSH IDLH
2-(2-butoxyethoxy)ethanol 112-34-5	TWA: 10 ppm inhalable fraction and vapor	-	-
Sodium Hydroxide 1310-73-2	Ceiling: 2 mg/m ³	TWA: 2 mg/m ³ (vacated) Ceiling: 2 mg/m ³	IDLH: 10 mg/m ³ Ceiling: 2 mg/m ³

NIOSH IDLH Immediately Dangerous to Life or Health

Other Information Vacated limits revoked by the Court of Appeals decision in AFL-CIO v. OSHA, 965 F.2d 962 (11th Cir., 1992).

Appropriate engineering controls

Engineering Controls Showers, Eyewash stations & Ventilation systems.

Individual protection measures, such as personal protective equipment

Eye/face protection Wear safety glasses with side shields (or goggles).

Skin and body protection Rubber gloves if prolonged contact and/or handling large volumes. Wear chemical resistant gloves.

Respiratory protection If exposure limits are exceeded or irritation is experienced, NIOSH/MSHA approved respiratory protection should be worn. Positive-pressure supplied air respirators may be required for high airborne contaminant concentrations. Respiratory protection must be provided in accordance with current local regulations.

General Hygiene Wear suitable gloves and eye/face protection.

9. PHYSICAL AND CHEMICAL PROPERTIES

Information on basic physical and chemical properties

Physical state Liquid
Appearance Slightly Opaque
Color Slightly Opaque
Odor Fresh & Clean
Odor threshold No Information available

<u>Property</u>	<u>Values</u>	<u>Remarks • Method</u>
pH	8.0-10.0	
Specific Gravity	1.0	

Viscosity	< 25 cP @ 25°C
Melting point/freezing point	No Information available
Flash point	Above 200°F
Boiling point / boiling range	99 °C / 210 ° F Degrees
Evaporation rate	No Information available
Flammability (solid, gas)	No data available
Flammability Limits in Air	
Upper flammability limit:	No Information available
Lower flammability limit:	No Information available
Vapor pressure	No Information available
Vapor density	No Information available
Water solubility	Complete
Partition coefficient	No Information available
Autoignition temperature	No Information available
Decomposition temperature	No Information available

Other Information

Density Lbs/Gal	8.33
VOC Content (%)	0.9

10. STABILITY AND REACTIVITY**Reactivity**

No data available

Chemical stability

Stable under recommended storage conditions.

Possibility of Hazardous Reactions

None under normal processing.

Conditions to avoid

Extremes of temperature and direct sunlight.

Incompatible materials

None known based on information supplied.

Hazardous Decomposition Products

None known based on information supplied.

11. TOXICOLOGICAL INFORMATION**Information on likely routes of exposure****Product Information**

Inhalation	Avoid breathing vapors or mists. May cause irritation of respiratory tract.
Eye contact	Avoid contact with eyes. Contact with eyes may cause irritation.
Skin Contact	Avoid contact with skin. Prolonged contact may cause redness and irritation.
Ingestion	Do not taste or swallow. May cause irritation in mouth and throat. May cause gastro intestinal irritation.

Information on toxicological effects**Symptoms** No Information available.**Delayed and immediate effects as well as chronic effects from short and long-term exposure**

Sensitization	No Information available.
Germ cell mutagenicity	No Information available.
Carcinogenicity	No Information available.
IARC (International Agency for Research on Cancer)	
Group 2A - Probably Carcinogenic to Humans	
OSHA (Occupational Safety and Health Administration of the US Department of Labor)	
X - Present	
Reproductive toxicity	No Information available.
STOT - single exposure	No Information available.
STOT - repeated exposure	No Information available.
Aspiration hazard	No Information available.

Numerical measures of toxicity - Product Information

Unknown Acute Toxicity 2.0105501% of the mixture consists of ingredient(s) of unknown toxicity

12. ECOLOGICAL INFORMATION

Ecotoxicity

0.01055% of the mixture consists of components(s) of unknown hazards to the aquatic environment

Chemical Name	Algae/aquatic plants	Fish	Crustacea
2-(2-butoxyethoxy)ethanol 112-34-5	100: 96 h Desmodesmus subspicatus mg/L EC50	1300: 96 h Lepomis macrochirus mg/L LC50 static	100: 48 h Daphnia magna mg/L EC50
Sodium Lauryl Sulfate 151-21-3	3.59 - 15.6: 96 h Pseudokirchneriella subcapitata mg/L EC50 static 30 - 100: 96 h Desmodesmus subspicatus mg/L EC50 117: 96 h Pseudokirchneriella subcapitata mg/L EC50 38: 96 h Desmodesmus subspicatus mg/L EC50 42: 96 h Desmodesmus subspicatus mg/L EC50 53: 72 h Desmodesmus subspicatus mg/L EC50	10.2 - 22.5: 96 h Pimephales promelas mg/L LC50 semi-static 10.8 - 16.6: 96 h Poecilia reticulata mg/L LC50 static 13.5 - 18.3: 96 h Poecilia reticulata mg/L LC50 semi-static 15 - 18.9: 96 h Pimephales promelas mg/L LC50 static 22.1 - 22.8: 96 h Pimephales promelas mg/L LC50 static 4.06 - 5.75: 96 h Lepomis macrochirus mg/L LC50 static 4.2 - 4.8: 96 h Lepomis macrochirus mg/L LC50 flow-through 4.3 - 8.5: 96 h Oncorhynchus mykiss mg/L LC50 static 5.8 - 7.5: 96 h Pimephales promelas mg/L LC50 static 6.2 - 9.6: 96 h Pimephales promelas mg/L LC50 8 - 12.5: 96 h Pimephales promelas mg/L LC50 static 9.9 - 20.1: 96 h Brachydanio rerio mg/L LC50 semi-static 1.31: 96 h Cyprinus carpio mg/L LC50 semi-static 4.2: 96 h Oncorhynchus mykiss mg/L LC50 4.5: 96 h Lepomis macrochirus mg/L LC50 4.62: 96 h Oncorhynchus mykiss mg/L LC50 flow-through 7.97: 96 h Brachydanio rerio mg/L LC50 flow-through	1.8: 48 h Daphnia magna mg/L EC50
Tetrasodium EDTA 64-02-8	1.01: 72 h Desmodesmus subspicatus mg/L EC50	41: 96 h Lepomis macrochirus mg/L LC50 static 59.8: 96 h Pimephales promelas mg/L LC50 static	-
Trisodium nitrilotriacetate 5064-31-3	-	175 - 225: 96 h Lepomis macrochirus mg/L LC50 static 560 - 1000: 96 h Oryzias latipes mg/L LC50 560 - 1000: 96 h Oryzias latipes mg/L LC50 semi-static	560 - 1000: 48 h Daphnia magna mg/L LC50

		560 - 1000: 96 h Poecilia reticulata mg/L LC50 560 - 1000: 96 h Poecilia reticulata mg/L LC50 semi-static 72 - 133: 96 h Oncorhynchus mykiss mg/L LC50 static 93 - 170: 96 h Pimephales promelas mg/L LC50 flow-through 114: 96 h Pimephales promelas mg/L LC50 252: 96 h Lepomis macrochirus mg/L LC50 470: 96 h Pimephales promelas mg/L LC50 static	
Sodium Hydroxide 1310-73-2	-	45.4: 96 h Oncorhynchus mykiss mg/L LC50 static	-

Persistence and degradability

No Information available.

Bioaccumulation

No Information available.

Other adverse effects

No Information available

13. DISPOSAL CONSIDERATIONS

Waste treatment methods

Disposal of wastes

Disposal should be in accordance with applicable regional, national and local laws and regulations.

Contaminated packaging

Do not reuse container.

This product contains one or more substances that are listed with the State of California as a hazardous waste.

14. TRANSPORT INFORMATION

The basic description below is specific to the container size. This information is provided for at a glance DOT information. Please refer to the container and/or shipping papers for the appropriate shipping description before tendering this material for shipment. For additional information, please contact the distributor listed in section 1 of this SDS.

DOT

Not regulated

TDG

Not regulated

15. REGULATORY INFORMATION

International Inventories

TSCA

Complies

DSL/NDSL

Complies

Legend:

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

US Federal Regulations

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

SARA 311/312 Hazard Categories

Acute health hazard	No
Chronic Health Hazard	No
Fire hazard	No
Sudden release of pressure hazard	No
Reactive Hazard	No

CWA (Clean Water Act)

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

CERCLA

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material

US State Regulations

California Proposition 65

This product has been evaluated and does not require warning labeling under California Proposition 65.

U.S. State Right-to-Know Regulations

Chemical Name	New Jersey	Massachusetts	Pennsylvania
Trisodium nitrilotriacetate 5064-31-3	-	X	-
Sodium Hydroxide 1310-73-2	X	X	X

U.S. EPA Label Information

EPA Pesticide Registration Number Not Applicable

16. OTHER INFORMATION

NFPA	Health hazards 1	Flammability 0	Instability 0	Physical and Chemical Properties - Personal protection B
HMIS	Health hazards 1	Flammability 0	Physical hazards 0	

Issue Date 02-Aug-2021
Revision Date 02-Aug-2021

Revision Note
No Information available

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

End of Safety Data Sheet