



# SAFETY DATA SHEET

Issue Date 22-Jan-2021

Revision Date 22-Jan-2021

Version 2

## 1. PRODUCT AND COMPANY IDENTIFICATION

### Product identifier

**Product Name** Marine Restroom Cleaner

### Other means of identification

**Product Code** Z198

**Synonyms** None

### Details of the supplier of the safety data sheet

**Company Name** Nyco Products Company  
5332 Dansher Road,  
Countryside, IL 60525  
(708) 579-8100  
nycoproducts.com

### Emergency telephone number

**Emergency Telephone** Chemtrec 1-800-424-9300

## 2. HAZARDS IDENTIFICATION

### Classification

#### **OSHA Regulatory Status**

This chemical is considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Skin corrosion/irritation	Category 3
Serious eye damage/eye irritation	Category 2

### Label elements

#### Emergency Overview

## Warning

#### **Hazard statements**

Causes mild skin irritation

Causes serious eye irritation



**Appearance** Clear Blue

**Physical state** Liquid

**Odor** Rain Fresh

#### **Precautionary Statements - Prevention**

Wash face, hands and any exposed skin thoroughly after handling

Wear protective gloves/protective clothing/eye protection/face protection

#### Precautionary Statements - Response

Specific Treatment (See Section 4 on the SDS)

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing

If eye irritation persists: Get medical advice/attention

IF ON SKIN: Wash with plenty of soap and water

If skin irritation occurs: Get medical advice/attention

IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing

Call a POISON CENTER or doctor/physician if you feel unwell

IF SWALLOWED: Rinse mouth. DO NOT induce vomiting

Drink plenty of water

Immediately call a POISON CENTER or doctor/physician

#### Precautionary Statements - Disposal

Disposal should be in accordance with applicable regional, national and local laws and regulations

#### Hazards not otherwise classified (HNOC)

##### Other Information

Unknown Acute Toxicity

0 % of the mixture consists of ingredient(s) of unknown toxicity

### 3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical Name	CAS No.	Weight-%	Trade Secret
Butyl 3-hydroxybutanoate	53605-94-0	1-5	*
Surfactant Blend	Proprietary	1-5	*
Sodium Laureth Sulfate	68585-34-2	1-5	*

\*The exact percentage (concentration) of composition has been withheld as a trade secret.

### 4. FIRST AID MEASURES

#### First aid measures

##### Skin Contact

Wash off immediately with plenty of water for at least 15 minutes. If skin irritation persists, call a physician.

##### Eye contact

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. If symptoms persist, call a physician.

##### Inhalation

Remove to fresh air. If symptoms persist, call a physician.

##### Ingestion

Do NOT induce vomiting. Rinse mouth. Drink plenty of water. Call a physician immediately.

##### Self-protection of the first aider

Use personal protective equipment as required.

#### Most important symptoms and effects, both acute and delayed

##### Symptoms

Any additional important symptoms and effects are described in Section 11: Toxicology Information.

#### Indication of any immediate medical attention and special treatment needed

##### Note to physicians

May cause sensitization of susceptible persons.

### 5. FIRE-FIGHTING MEASURES

#### Suitable extinguishing media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

**Unsuitable extinguishing media** Caution: Use of water spray when fighting fire may be inefficient.

**Specific hazards arising from the chemical**

In the event of fire and/or explosion do not breathe fumes. May cause sensitization by inhalation and skin contact. Thermal decomposition can lead to release of irritating and toxic gases and vapors.

**Explosion data**

**Sensitivity to Mechanical Impact** None.

**Sensitivity to Static Discharge** None.

**Protective equipment and precautions for firefighters**

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

## 6. ACCIDENTAL RELEASE MEASURES

**Personal precautions, protective equipment and emergency procedures**

**Personal precautions** Avoid contact with eyes and skin. Use personal protective equipment as required.

**Environmental precautions**

**Environmental precautions** Do not allow into any storm sewer drains, lakes, streams, ponds, estuaries, oceans or other surface water bodies. Should not be released into the environment. Dispose of according to all local city, state and federal rules and regulations.

**Methods and material for containment and cleaning up**

**Methods for containment** Prevent further leakage or spillage if safe to do so.

**Methods for cleaning up** Soak up with inert absorbent material. Pick up and transfer to properly labeled containers. After cleaning, flush away traces with water. Prevent product from entering drains.

## 7. HANDLING AND STORAGE

**Precautions for safe handling**

**Advice on safe handling** Ensure adequate ventilation, especially in confined areas. Use personal protective equipment as required.

**Conditions for safe storage, including any incompatibilities**

**Storage Conditions** Keep out of the reach of children. Keep containers tightly closed in a cool, well-ventilated place.

**Incompatible materials** None known based on information supplied.

## 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

**Control parameters****Appropriate engineering controls**

**Engineering Controls** Showers, Eyewash stations & Ventilation systems.

**Individual protection measures, such as personal protective equipment**

**Eye/face protection** Wear safety glasses with side shields (or goggles).

**Skin and body protection** Wear chemical resistant gloves.

**Respiratory protection** Ensure adequate ventilation, especially in confined areas. If irritation is experienced, move to a well ventilated area.

**General Hygiene** When using do not eat, drink or smoke. Wash contaminated clothing before reuse.

## 9. PHYSICAL AND CHEMICAL PROPERTIES

### Information on basic physical and chemical properties

<b>Physical state</b>	Liquid
<b>Appearance</b>	Clear Blue
<b>Color</b>	Blue
<b>Odor</b>	Rain Fresh
<b>Odor threshold</b>	No Information available

<u>Property</u>	<u>Values</u>	<u>Remarks • Method</u>
pH	6.0 - 8.0	
Specific Gravity	1.008	
Viscosity	< 25 cP @ 25°C	
Melting point/freezing point	No Information available	
Flash point	Above 200°F	
Boiling point / boiling range	100 °C / 212 ° F Degrees	
Evaporation rate	No Information available	
Flammability (solid, gas)	No data available	
Flammability Limits in Air		
Upper flammability limit:	No Information available	
Lower flammability limit:	No Information available	
Vapor pressure	No Information available	
Vapor density	No Information available	
Water solubility	Complete	
Partition coefficient	No Information available	
Autoignition temperature	No Information available	
Decomposition temperature	No Information available	

### Other Information

Density Lbs/Gal	8.40
VOC Content (%)	Not Applicable

## 10. STABILITY AND REACTIVITY

### Reactivity

No data available

### Chemical stability

Stable under recommended storage conditions.

### Possibility of Hazardous Reactions

None under normal processing.

### Conditions to avoid

Extremes of temperature and direct sunlight.

### Incompatible materials

None known based on information supplied.

### Hazardous Decomposition Products

None known based on information supplied.

## 11. TOXICOLOGICAL INFORMATION

### Information on likely routes of exposure

Product Information

<b>Inhalation</b>	Avoid breathing vapors or mists. May cause irritation of respiratory tract.
<b>Eye contact</b>	Avoid contact with eyes. Causes serious eye irritation.
<b>Skin Contact</b>	Avoid contact with skin. Prolonged or repeated contact may dry skin and cause irritation.
<b>Ingestion</b>	Do not taste or swallow. May cause stomach distress, nausea, or vomiting.

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
Butyl 3-hydroxybutanoate 53605-94-0	> 5000 MG/KG ( Rat )	> 5000 mg/kg ( Rat )	-
Surfactant Blend	> 5000 mg/kg ( Rat )	> 2000 mg/kg ( Rabbit )	-

**Information on toxicological effects**

**Symptoms** No Information available.

**Delayed and immediate effects as well as chronic effects from short and long-term exposure**

<b>Irritation</b>	MAY CAUSE SKIN IRRITATION.
<b>Sensitization</b>	No Information available.
<b>Germ cell mutagenicity</b>	No Information available.
<b>Carcinogenicity</b>	No Information available.
<b>Reproductive toxicity</b>	No Information available.
<b>STOT - single exposure</b>	No Information available.
<b>STOT - repeated exposure</b>	No Information available.
<b>Chronic toxicity</b>	Repeated contact may cause allergic reactions in very susceptible persons. Avoid repeated exposure.
<b>Aspiration hazard</b>	No Information available.

**Numerical measures of toxicity - Product Information**

**Unknown Acute Toxicity** 0 % of the mixture consists of ingredient(s) of unknown toxicity

## 12. ECOLOGICAL INFORMATION

**Ecotoxicity**

0% of the mixture consists of components(s) of unknown hazards to the aquatic environment

Chemical Name	Algae/aquatic plants	Fish	Crustacea
Butyl 3-hydroxybutanoate 53605-94-0	-	100: 96 h Rainbow Trout mg/L LC50	100: 48 h Daphnia magna mg/L LC50
Surfactant Blend	-	>100: 96 h Brachydanio Rerio mg/L LC50	>100: 48 h Daphnia Magna mg/L EC50
Trisodium Citrate Dihydrate 6132-04-3	-	18000 - 32000: 96 h Poecilia reticulata mg/L LC50	5600 - 10000: 48 h Daphnia magna mg/L EC50
Sodium Sulfate 7757-82-6	-	3040 - 4380: 96 h Lepomis macrochirus mg/L LC50 static 13500: 96 h Lepomis macrochirus mg/L LC50 13500 - 14500: 96 h Pimephales promelas mg/L LC50 6800: 96 h Pimephales promelas mg/L LC50 static	2564: 48 h Daphnia magna mg/L EC50 630: 96 h Daphnia magna mg/L EC50

**Persistence and degradability**

No Information available.

**Bioaccumulation**

No Information available.

**Other adverse effects**

No Information available

### 13. DISPOSAL CONSIDERATIONS

#### Waste treatment methods

<b>Disposal of wastes</b>	Disposal should be in accordance with applicable regional, national and local laws and regulations.
<b>Contaminated packaging</b>	Do not reuse container.

### 14. TRANSPORT INFORMATION

The basic description below is specific to the container size. This information is provided for at a glance DOT information. Please refer to the container and/or shipping papers for the appropriate shipping description before tendering this material for shipment. For additional information, please contact the distributor listed in section 1 of this SDS.

<b><u>DOT</u></b>	Not regulated
<b><u>TDG</u></b>	Not regulated

### 15. REGULATORY INFORMATION

#### International Inventories

<b>TSCA</b>	Complies
<b>DSL/NDSL</b>	Complies

#### Legend:

**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory  
**DSL/NDSL** - Canadian Domestic Substances List/Non-Domestic Substances List

#### US Federal Regulations

##### **SARA 313**

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

##### **SARA 311/312 Hazard Categories**

<b>Acute health hazard</b>	Yes
<b>Chronic Health Hazard</b>	No
<b>Fire hazard</b>	No
<b>Sudden release of pressure hazard</b>	No
<b>Reactive Hazard</b>	No

##### **CWA (Clean Water Act)**

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

##### **CERCLA**

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material

#### US State Regulations

##### **California Proposition 65**

This product has been evaluated and does not require warning labeling under California Proposition 65.

**U.S. State Right-to-Know Regulations**

Chemical Name	New Jersey	Massachusetts	Pennsylvania
Sodium Sulfate 7757-82-6	-	X	X

**U.S. EPA Label Information**

EPA Pesticide Registration Number Not Applicable

**16. OTHER INFORMATION**

<b>NFPA</b>	Health hazards 2	Flammability 0	Instability 0	Physical and Chemical Properties -
<b>HMIS</b>	Health hazards 2	Flammability 0	Physical hazards 0	Personal protection B

Issue Date 22-Jan-2021

Revision Date 22-Jan-2021

**Revision Note**

No Information available

**Disclaimer**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

**End of Safety Data Sheet**