



The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.



Main

| | |
|---|--|
| Range | TeSys |
| Product name | TeSys D |
| Product or component type | Reversing contactor |
| Device short name | LC2D |
| Contactor application | Resistive load Motor control |
| Utilisation category | AC-1 AC-3 |
| Device presentation | Preassembled with reversing power busbar |
| Poles description | 3P |
| Power pole contact composition | 3 NO |
| [Ue] rated operational voltage | Power circuit <= 1000 V AC 25...400 Hz Power circuit <= 300 V DC |
| [Ie] rated operational current | 125 A 140 °F (60 °C) <= 440 V AC AC-1 power circuit 80 A 140 °F (60 °C) <= 440 V AC AC-3 power circuit |
| Motor power kW | 22 KW 220...230 V AC 50 Hz 37 KW 380...400 V AC 50 Hz 45 KW 415...440 V AC 50 Hz 55 KW 500 V AC 50 Hz 45 KW 660...690 V AC 50 Hz 45 kW 1000 V AC 50 Hz |
| Motor power HP (UL / CSA) | 20 Hp 200/208 V at AC 60 Hz for 3 phase 7.5 Hp 115 V at AC 60 Hz for 1 phase 15 Hp 230/240 V at AC 60 Hz for 1 phase 25 Hp 230/240 V at AC 60 Hz for 3 phase 60 Hp 460/480 V at AC 60 Hz for 3 phase 60 hp 575/600 V at AC 60 Hz for 3 phase |
| Control circuit type | AC 50/60 Hz |
| [Uc] control circuit voltage | 120 V AC 50/60 Hz |
| Auxiliary contact composition | 1 NO + 1 NC |
| [Uimp] rated impulse withstand voltage | 8 kV IEC 60947 |
| Overvoltage category | III |
| [Ith] conventional free air thermal current | 10 A 140 °F (60 °C) signalling circuit 125 A 140 °F (60 °C) power circuit |
| Irms rated making capacity | 140 A AC signalling circuit IEC 60947-5-1 250 A DC signalling circuit IEC 60947-5-1 1100 A 440 V power circuit IEC 60947 |
| Rated breaking capacity | 1100 A 440 V power circuit IEC 60947 |
| [Icw] rated short-time withstand current | 135 A 104 °F (40 °C) - 10 min power circuit 320 A 104 °F (40 °C) - 1 min power circuit 640 A 104 °F (40 °C) - 10 s power circuit 990 A 104 °F (40 °C) - 1 s power circuit 100 A - 1 s signalling circuit 120 A - 500 ms signalling circuit 140 A - 100 ms signalling circuit |
| Associated fuse rating | 10 A gG signalling circuit IEC 60947-5-1 200 A gG <= 690 V type 1 power circuit 160 A gG <= 690 V type 2 power circuit |
| Average impedance | 0.8 mOhm - Ith 125 A 50 Hz power circuit |
| [Ui] rated insulation voltage | Power circuit 600 V CSA Power circuit 600 V UL Signalling circuit 690 V IEC 60947-1 Signalling circuit 600 V CSA Signalling circuit 600 V UL Power circuit 1000 V IEC 60947-4-1 |
| Electrical durability | 0.8 Mcycles 125 A AC-1 <= 440 V 1.5 Mcycles 80 A AC-3 <= 440 V |

| | |
|----------------------------|--|
| Power dissipation per pole | 12.5 W AC-1 5.1 W AC-3 |
| Front cover | With |
| Interlocking type | Mechanical |
| Mounting support | Plate Rail |
| Standards | CSA C22.2 No 14 EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 UL 508 |
| Product certifications | DNV CSA UL LROS (Lloyds register of shipping) GL RINA GOST BV CCC |
| Connections - terminals | Control circuit screw clamp terminals 1 0.00... 0.01 in ² (1...4 mm ²)flexible without cable end Control circuit screw clamp terminals 2 0.00... 0.01 in ² (1...4 mm ²)flexible without cable end Control circuit screw clamp terminals 2 0.00... 0.00 in ² (1...2.5 mm ²)flexible with cable end Control circuit screw clamp terminals 1 0.00... 0.01 in ² (1...4 mm ²)solid Control circuit screw clamp terminals 2 0.00... 0.01 in ² (1...4 mm ²)solid Control circuit screw clamp terminals 1 0.00... 0.00 in ² (1...2.5 mm ²)flexible with cable end Power circuit connector 1 0.01...0.08 in ² (4... 50 mm ²)flexible without cable end Power circuit connector 2 0.01...0.04 in ² (4... 25 mm ²)flexible without cable end Power circuit connector 1 0.01...0.08 in ² (4... 50 mm ²)flexible with cable end Power circuit connector 2 0.01...0.02 in ² (4... 16 mm ²)flexible with cable end Power circuit connector 1 0.01...0.08 in ² (4... 50 mm ²)solid Power circuit connector 2 0.01...0.04 in ² (4... 25 mm ²)solid |
| Tightening torque | Control circuit 10.62 lbf.in (1.2 N.m) screw clamp terminals flat Ø 6 mm Control circuit 10.62 lbf.in (1.2 N.m) screw clamp terminals Philips No 2 Power circuit 106.21 lbf.in (12 N.m) connector flat Ø 6 to Ø 8 mm Power circuit 106.21 lbf.in (12 N.m) connector hexagonal 0.16 in (4 mm) |
| Operating time | 20...35 ms closing 6...20 ms opening |
| Safety reliability level | B10d = 1369863 cycles contactor with nominal load EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load EN/ISO 13849-1 |
| Mechanical durability | 4 Mcycles |
| Maximum operating rate | 3600 cyc/h 140 °F (60 °C) |

Complementary

| | |
|---------------------------------|---|
| Coil technology | Without built-in suppressor module |
| Control circuit voltage limits | 0.3...0.6 Uc -40...158 °F (-40...70 °C) drop-out AC 50/60 Hz 0.8...1.1 Uc -40...131 °F (-40...55 °C) operational AC 50 Hz 0.85...1.1 Uc -40...131 °F (-40...55 °C) operational AC 60 Hz 1...1.1 Uc 131...158 °F (55...70 °C) operational AC 50/60 Hz |
| Inrush power in VA | 245 VA 60 Hz 0.75 68 °F (20 °C)) 245 VA 50 Hz 0.75 68 °F (20 °C)) |
| Hold-in power consumption in VA | 26 VA 60 Hz 0.3 68 °F (20 °C)) 26 VA 50 Hz 0.3 68 °F (20 °C)) |
| Heat dissipation | 6...10 W 50/60 Hz |
| Auxiliary contacts type | Mechanically linked 1 NO + 1 NC IEC 60947-5-1 Mirror contact 1 NC IEC 60947-4-1 |
| Signalling circuit frequency | 25...400 Hz |
| Minimum switching current | 5 mA signalling circuit |
| Minimum switching voltage | 17 V signalling circuit |
| Non-overlap time | 1.5 Ms on de-energisation between NC and NO contact 1.5 ms on energisation between NC and NO contact |
| Insulation resistance | > 10 MOhm signalling circuit |

Environment

| | |
|---------------------------------------|---|
| IP degree of protection | IP20 front face IEC 60529 |
| Protective treatment | TH IEC 60068-2-30 |
| Pollution degree | 3 |
| Ambient air temperature for operation | -40...140 °F (-40...60 °C) 140...158 °F (60...70 °C) with derating |
| Ambient air temperature for storage | -76...176 °F (-60...80 °C) |
| Operating altitude | 0...9842.52 ft (0...3000 m) |
| Fire resistance | 1562 °F (850 °C) IEC 60695-2-1 |
| Flame retardance | V1 conforming to UL 94 |
| Mechanical robustness | Vibrations contactor open: 2 Gn, 5...300 Hz Shocks contactor open: 8 Gn for 11 ms Vibrations contactor closed: 3 Gn, 5...300 Hz Shocks contactor closed: 10 Gn for 11 ms |
| Height | 5.00 in (127 mm) |
| Width | 7.17 in (182 mm) |
| Depth | 6.22 in (158 mm) |
| Net Weight | 7.05 lb(US) (3.2 kg) |

Ordering and shipping details

| | |
|-----------------------|---|
| Category | 22359 - CTR, TESYS D, OPEN, 80-150A AC&DC |
| Discount Schedule | I12 |
| GTIN | 00785901457190 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 8.22 lb(US) (3.73 kg) |
| Returnability | Yes |
| Country of origin | CZ |

Packing Units

| | |
|------------------------|-------------------|
| Unit Type of Package 1 | PCE |
| Package 1 Height | 7.28 in (18.5 cm) |
| Package 1 width | 7.48 in (19 cm) |
| Package 1 Length | 10.24 in (26 cm) |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |
| PVC free | Yes |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|