



Main

Range	Spacial
Accessory / separate part category	Enclosure accessory
Product or component type	Door
Application	Multi-purpose
For enclosure nominal dimensions	-
Mounting location	Front Side
Range compatibility	Spacial SF
Device composition	4 locking bar catches 1 locking bar system 4 points 1 lock with handle and 5 mm double bar insert 1 door 4 hinges
Quantity per set	Set of 1

Complementary

Material	Sheet steel
Color	Gray RAL 7035)
Surface finish	Epoxy-polyester powder
Lock type	Lock 5 mm double bar
Number of locks	1
Door type	External plain
Door opening side	Reversible 120 °)
Height	Nominal 78.74 in (2000 mm)
Width	Nominal 15.75 in (400 mm)

Ordering and shipping details

Category	80035 - ENCLOSURE SYSTEMS FLOOR MOUNT
Discount Schedule	ES1
GTIN	00785901949992
Nbr. of units in pkg.	1
Package weight(Lbs)	46.2 lb(US) (20.96 kg)
Returnability	Yes
Country of origin	ES

Packing Units

Package 1 Height	2.17 in (55.000 mm)
Package 1 width	14.76 in (375.000 mm)
Package 1 Length	82.09 in (2085.000 mm)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------