



### Main

Range	Thalassa
Product name	Thalassa PLM
Device short name	PLM
Enclosure type	Multi-purpose
Category	Compact enclosure
Nominal height	33.35 in (847 mm)
Nominal width	25.04 in (636 mm)
Nominal depth	11.81 in (300 mm)
Enclosure mounting	Wall mounted
Device composition	1 body 1 door 2 lock
Door type	Solid
Lock type	3 mm double-bar lock

### Complementary

Number of locks	2
Mounting plate description	Without mounting plate
Accessibility for operation	Front
Removable parts	Door by hinges
Material	Polyester reinforced with fibreglass
Color	Grey (RAL 7035)
Standards	IEC 62208 NEMA classification 4X NEMA classification 13
Product certifications	UL
Electrical insulation class	Class II

### Environment

IP degree of protection	IP66 IEC 60529
IK degree of protection	IK10 IEC 62262
Fire resistance	1760 °F (960 °C) IEC 62208
Ambient air temperature for operation	-40...176 °F (-40...80 °C)

### Ordering and shipping details

Category	80034 - ENCLOSURE SYSTEMS WALL MOUNT METAL
Discount Schedule	ES1
GTIN	00785901073741
Nbr. of units in pkg.	1
Package weight(Lbs)	38.89 lb(US) (17.64 kg)
Returnability	Yes
Country of origin	ES

### Packing Units

Package 1 Height	36.50 in (927.100 mm)
Package 1 width	13.30 in (337.820 mm)
Package 1 Length	26.30 in (668.020 mm)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>