


## Valuable features, varying by model

- Touchscreen display
- Intuitive wake/leave/return/sleep programming icons
- On/off filter change reminder
- Auto changeover
- Smartphone accessibility via Robertshaw app (iOS/Android)
- Alexa compatibility



## WALL THERMOSTATS

Simple | Powerful | Economical



RS9110

RS8210/RS9210



RS9110T/RS9320T



RS8110



RS10420T



RS9110/RS9220



## Offer simple, powerful command—fast

### A wide spectrum of control

This line of non-programmable, programmable and WiFi models suits nearly any single- or multi-stage heating and cooling system.

### User-friendly design

Large, easy-to-read blue backlit displays and simple programming menus make these units easy to navigate and operate. Adjustable temperature differential (swing) and other functions put owners in control.

### Easy installation

With features such as universal sub-bases, these units install quickly and give owners comfort control in no time.

## Feature-rich models offer unique value



Customer Service +1.800.304.6563  
HVACCustomerService@robertshaw.com  
www.robertshaw.com

©2021 Robertshaw  
2/21 -150-2808

Robertshaw.com



# Pro-Series

## Find the Right Model for Your Project

Model	5-1-1 Programmable	7-day Programmable	Heating Stages	Cooling Stages	Suits heat pump – no aux/ emergency heat	Suits heat pump with aux/emergency heat	System Fuel Source: Gas, Electric or Oil	Suits millivolt applications	Wall or junction box mount	Touchscreen display	Keypad lockout	Adjustable differential (swing) control	Auto changeover	Adjustable temperature calibration	Adjustable setpoint limits	Minimum compressor run time	Compressor delay – short-cycling prevention	Filter change reminder	WiFi/smart phone accessible	24V Hardwire (C Terminal)	DC 2 x AAA 1.5V Alkaline Batteries (Included)	Terminals
RS8110			1	1	•		•	•	•			•		•	•		•			•	•	Rh, Rc, C, Y, W, G, O, B
RS8210			2	1	•	•	•	•	•			•		•	•		•	•		•	•	R, C, Y, W2, W/E, G, O, B
RS9110	•	•	1	1	•		•	•	•			•		•	•		•	•		•	•	Rh, Rc, C, Y, W, G, O, B
RS9210	•	•	2	1	•	•	•	•	•			•		•	•		•	•		•	•	R, C, Y, W2, W/E, G, O, B
RS9220	•	•	2	2	•		•	•	•			•		•	•		•	•		•	•	Rh, Rc, C, Y, Y2, W, W2, G, O, B
RS9110T	•	•	1	1	•		•	•	•	•	•	•	•	•	•	•	•	•		•	•	Rh, Rc, C, Y, W, G, O, B
RS9320T	•	•	3 <sup>a</sup>	2 <sup>a</sup>	•	•	•	•	•	•	•	•	•	•	•		•	•		•	•	Rh, Rc, C, Y, Y2, W/E, W2, G, O, B
RS10420T	•	•	4 <sup>b</sup>	2 <sup>b</sup>	•	•	•		•	•	•	•	•	•	•		•	•	•	•		Rh, Rc, C, Y, Y2, W/E, W2, G, O, B

<sup>ab</sup> With heat pump; 2-stage conventional without heat pump



**6** Year Limited Warranty

Customer Service 800.304.6563

Robertshaw.com