

SAFETY DATA SHEET

Issue Date 05-Feb-2013 Revision Date 05-Feb-2013 Version 1

1. IDENTIFICATION

Product Identifier

Product Name WipesPlus® Patient Washcloths

Other means of identification

SDS # 37605

Product Code 37605

Recommended use of the chemical and restrictions on use

Recommended Use Disposable washcloth for bathing of patients in medical and geriatric care settings

Details of the supplier of the safety data sheet

Supplier Address

WipesPlus® Progressive Products, LLC 4 International Drive, Suite 224

Rye Brook, NY 10573

Emergency telephone number

Company Phone Number Phone: 1-914-939-1864

Fax: 1-888-272-5574

Emergency Telephone INFOTRAC 1-352-323-3500 (International)

1-800-535-5053 (North America)

2. HAZARDS IDENTIFICATION

Classification

This chemical does not meet the hazardous criteria set forth by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.122). However, this Safety Data Sheet (SDS) contains valuable information critical to the safe handling and proper use of this product. This SDS should be retained and available for employees and other users of this product

The product contains no substances which at their given concentration, are considered to be hazardous to health

Appearance Liquid saturated on wipe Physical state liquid

Hazards not otherwise classified (HNOC)
Not Applicable
Other Information
Not Applicable

3. COMPOSITION/INFORMATION ON INGREDIENTS

Ingredients not listed on this safety data sheet are considered to be non-hazardous according to OSHA 1910.1200.

Chemical Name	CAS No	Weight-%	Trade Secret
Quaternium-15	51229-78-8	1.42	*
Methylchloro-Iso-Thiazolinone	247-500-7		*
Methylisothiazolinone	220-239-6	.95	*

4. FIRST AID MEASURES

First aid measures

Inhalation If symptoms are experienced, remove source of contamination or move victim to fresh air. If

symptoms persist, call a physician.

Eye contact Immediately flush with plenty of water. After initial flushing, remove any contact lenses and

continue flushing for at least 15 minutes. If eye irritation persists: Get medical

advice/attention.

Ingestion Call a physician or poison control center immediately. Give one or two glasses of water if

patient is alert and able to swallow. Do NOT induce vomiting. Never give anything by mouth

to an unconscious person.

Skin Contact If irritation occurs and product is on the skin, rinse thoroughly with lukewarm water, followed

by a thorough washing of the affected area with soap and water. If skin irritation persists,

call a physician.

Most important symptoms and effects, both acute and delayed

Symptoms Direct eye contact may cause stinging, tearing and redness. May cause irritation to the

mucous membranes and upper respiratory tract. May cause discomfort if swallowed.

Indication of any immediate medical attention and special treatment needed

Note to physicians Treat symptomatically.

5. FIRE-FIGHTING MEASURES

Suitable Extinguishing Media

Water spray (fog). Foam. Dry chemical. Carbon dioxide (CO2).

Unsuitable Extinguishing Media Not determined.

Specific hazards arising from the chemical

None known.

Hazardous combustion products Burning after dehydration may produce ammonia, carbon monoxide and/or carbon dioxide

Protective equipment and precautions for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal precautionsUse personal protective equipment as required.

Environmental precautions Prevent entry into waterways, sewers, basements or confined areas. See Section 12 for

additional ecological information.

Methods and material for containment and cleaning up

Methods for containment Prevent further leakage or spillage if safe to do so.

Methods for cleaning upSmall Spills: Flush area of spill with copious amounts of water.

7. HANDLING AND STORAGE

Precautions for safe handling

Advice on safe handling Handle in accordance with good industrial hygiene and safety practice.

Conditions for safe storage, including any incompatibilities

Storage Conditions Keep containers tightly closed in a dry, cool and well-ventilated place. Store in a dry place

no lower in temperature than 50°F or higher than 120°F. Do not contaminate water, food, or

feed by storage or disposal.

Incompatible materials None Known.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Exposure Guidelines

Appropriate engineering controls

Engineering Controls Eyewash stations. Showers.

Individual protection measures, such as personal protective equipment

Eye/face protection Avoid contact with eyes.

Skin and body protectionNo special technical protective measures are necessary.

Respiratory protection For reasonable uses of this material, respiratory protection should not be necessary.

General Hygiene Considerations Handle in accordance with good industrial hygiene and safety practice.

9. PHYSICAL AND CHEMICAL PROPERTIES

Information on basic physical and chemical properties

Physical state liquid

AppearanceLiquid saturated on wipeOdorNot determinedColorNot determinedOdor thresholdNot determined

Remarks • Method

Property
pH (at 25 °C)

Melting point/freezing point

Values

5.5 to 6.5

Not determined

Boiling point/boiling range 100 ℃ Flash point None

Evaporation rate (1) (AS WATER) Flammability (solid, gas) Not determined

Flammability Limits in Air

Upper flammability limits Not determined Lower flammability limit Not determined Vapor pressure Not determined Vapor density Not determined Specific Gravity (at 25 °C) 1.015 to 1.017 Water solubility Complete Solubility in other solvents Not determined Partition coefficient Not determined **Autoignition temperature** Not determined **Decomposition temperature** Not determined Kinematic viscosity Not determined Dynamic viscosity Not determined **Explosive properties** Not determined **Oxidizing properties** Not determined

Other Information

10. STABILITY AND REACTIVITY

Reactivity

Not reactive under normal conditions

Chemical stability

Stable under recommended storage conditions.

Possibility of Hazardous Reactions

None under normal processing.

Conditions to avoid

Keep out of reach of children.

Incompatible materials

None Known.

Hazardous Decomposition Products

Burning after dehydration may produce ammonia, carbon monoxide and/or carbon dioxide.

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure

Product Information

Inhalation Under normal conditions of intended use, this material is not expected to be an inhalation

hazard.

Eye contact Avoid contact with eyes.

Skin Contact No known hazard in contact with skin.

Ingestion Do not taste or swallow.

Component Information

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
Quaternium-15	1150 mg/kg	-	-
51229-78-8			
Methylchloro-Iso-Thiazolinone	30 mg/kg	-	-
& Methylisothiazolinone			
247-500-7			
220-239-6			

Information on physical, chemical and toxicological effects

Symptoms Please see section 4 of this SDS for symptoms.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Carcinogenicity Carcinogenic potential is unknown.

Numerical measures of toxicity- Product

Not determined

12. ECOLOGICAL INFORMATION

Ecotoxicity

Not regarded as dangerous for the environment

Persistence and degradability

Not determined.

Bioaccumulation

Not determined.

Mobility

Not determined.

Other adverse effects Not determined

13. DISPOSAL CONSIDERATIONS

Waste treatment methods

Disposal of wastesDisposal should be in accordance with applicable regional, national and local laws and

regulations.

Contaminated packaging Disposal should be in accordance with applicable regional, national and local laws and

regulations.

14. TRANSPORT INFORMATION

DOT Not regulated

IATA Not regulated

IMDG Not regulated

15. REGULATORY INFORMATION

16. OTHER INFORMATION

NFPA Health hazards Flammability Instability Special Hazards Not

1 0 0 determined

HMIS Health Flammability Physical hazards Personal protection

hazards 1

2

Issue Date 05-Feb-2013

Revision Date

05-Feb-2013

Revision Note new format

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

End of Safety Data Sheet