



Main

| | |
|--------------|--------------------------------|
| Product Type | Industrial Control Transformer |
| Power Rating | 50 VA |
| Type | T |

Complementary

| | |
|--------------------------------|-----------------------|
| Number of Phases | 1 phase |
| Power Rating | 50 VA |
| Temperature Rise | 55 °C |
| Electrical Connection | Screw clamp terminals |
| Fingersafe Cover Compatibility | FSC1 |

Environment

| | |
|------------------------|-------------------------|
| Certifications | CSA UL Listed |
| Enclosure Type | Not rated (open device) |
| Insulation Temperature | 221 °F (105 °C) |

Ordering and shipping details

| | |
|-----------------------|-----------------------------|
| Category | 16206 - 9070 T (NOT TF) MTO |
| Discount Schedule | CP8 |
| GTIN | 00785901688976 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 1 lb(US) (0.45 kg) |
| Returnability | Yes |
| Country of origin | US |

Packing Units

| | |
|------------------|---------------------|
| Package 1 Height | 3.80 in (9.652 cm) |
| Package 1 width | 4.00 in (10.160 cm) |
| Package 1 Length | 4.20 in (10.668 cm) |


Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| PVC free | Yes |


Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Approximate Dimensions



in.
[mm]



Connections and Wiring Diagrams

Voltage and Connection Options

| Voltage Code | Voltages | | Connections | |
|--------------|-----------|---|---|---|
| | Primary | Secondary | Primary | Secondary |
| D13 | 120 | 12/24 | Connect to H1 and H2 | 12: Connect to X1 and X4 Jumper X1 with X3 Jumper X2 with X4 24: Connect to X1 and X4 Jumper X2 with X3 |
| D36 | 600 | | Connect to H1 and H2 | |
| D54 | 120 x 240 | | 120: Connect to H1 and H4 Jumper H1 with H3 Jumper H2 with H4 | |
| | | | 240: Connect to H1 and H4 Jumper H2 with H3 | |
| D59 | 240 x 480 | 240: Connect to H1 and H4 Jumper H1 with H3 Jumper H2 with H4 480: Connect to H1 and H4 Jumper H2 with H3 | | |

