

ELM250JD

Earth leakage module, PowerPacT J,
micrologic add-on ground fault modules, 150 to
250 A



Main

Range of product	Powerpact
Product or component type	Earth leakage add-on block
Circuit breaker type	JL JJ JD JG

Complementary

Line Rated Current	150...250 A
Network type	AC
[Ue] rated operational voltage	240...600 V
Earth-leakage sensitivity	30 MA 3000 MA 1000 MA 300 MA 100 mA
Earth-leakage protection time delay	Instantaneous 500 ms
Local signalling	Trip indicator
Electrical connection to mcb	Plug in
Tightening torque	228.35 lbf.in (25.8 N.m) 0.04...0.29 in ² (25...185 mm ²) (AWG 4...350 kcmil)

Environment

Product certifications	UL CSA
------------------------	-----------

Ordering and shipping details

Category	00916-GROUND FAULT EQUIPMENT
Discount Schedule	DE2
GTIN	00785901684749
Nbr. of units in pkg.	1
Package weight(Lbs)	4.06 lb(US) (1.842 kg)
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	6.40 in (16.256 cm)
Package 1 width	5.30 in (13.462 cm)
Package 1 Length	10.60 in (26.924 cm)

Offer Sustainability

California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov
EU RoHS Directive	Not compliant
China RoHS Regulation	 China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------