

EZM1EXT6

EZ Meter Pak, 6 inch bus extension, 1200 A bus, 120/240 VAC single phase



Main

Device short name	EZ
Range of product	Meter-Pak

Complementary

Line Rated Current	1200 A
[Ue] rated operational voltage	120/240 V AC
Bus rated current	1200 A
Device mounting	Surface
Enclosure material	Steel
Number of Phases	1 phase
Product certifications	UL Listed
Height	11.66 in (296.16 mm)
Width	19.34 in (491.24 mm)
Depth	6.37 in (161.80 mm)

Environment

Enclosure Rating	NEMA 1
------------------	--------

Ordering and shipping details

Category	00027 - METERING ACCESSORIES
Discount Schedule	DE4
GTIN	00785901889892
Nbr. of units in pkg.	1
Package weight(Lbs)	19.83 lb(US) (8.99 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Package 1 Height	7.30 in (18.542 cm)
Package 1 width	14.40 in (36.576 cm)
Package 1 Length	21.00 in (53.340 cm)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes

Contractual warranty

Warranty	18 months
----------	-----------