

# JRA36250

Circuit breaker, PowerPacT J, I-Line, thermal-magnetic, 250A, 3 pole, 100 kA, 600 VAC, phase ABC



## Main

|                           |                 |
|---------------------------|-----------------|
| Product or component type | Circuit breaker |
|---------------------------|-----------------|

## Complementary

|                           |  |
|---------------------------|--|
| Number of Poles           | 3P   |
| Breaking capacity code    | R  |
| Magnetic hold current     | 1250 A   |
| Magnetic tripping current | 2500 A   |
| Electrical connection     | I-Line connection line<br>Lugs load  |
| Tightening torque         | 230.12 lbf.in (26 N.m) 0.15...0.29 in <sup>2</sup> (95...185 mm <sup>2</sup> ) (AWG 3/0...350 kcmil) |
| Phase connection          | ABC  |
| Height                    | 11.48 in (291.59 mm)   |
| Width                     | 4.48 in (113.79 mm)  |
| Depth                     | 5.87 in (149.10 mm)  |
| Continuous current rating | 80 %   |

## Ordering and shipping details

|                       |   |
|-----------------------|---|
| Category              | 01109 - H/J HIGH INTERRUPT I-LINE CB/SW |
| Discount Schedule     | DE2                                     |
| GTIN                  | 00785901266556                          |
| Nbr. of units in pkg. | 1                                       |
| Package weight(Lbs)   | 6.85 lb(US) (3.11 kg)                   |
| Returnability         | No                                      |
| Country of origin     | US                                      |

## Packing Units

|                  |                      |
|------------------|----------------------|
| Package 1 Height | 5.90 in (14.986 cm)  |
| Package 1 width  | 8.40 in (21.336 cm)  |
| Package 1 Length | 14.70 in (37.338 cm) |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

|                            |  |
|----------------------------|--|
| Sustainable offer status   | Green Premium product  |
| California proposition 65  | WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| EU RoHS Directive          | Compliant <a href="#">EU RoHS Declaration</a>  |
| Mercury free               | Yes  |
| RoHS exemption information | <a href="#">Yes</a>  |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>   |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>  |
| Circularity Profile        | <a href="#">End Of Life Information</a>  |
| PVC free                   | Yes  |