



### Main

Product or component type	Automatic switch
Range of product	PowerPact H
Trip unit technology	Magnetic

### Complementary

Line Rated Current	150 A
[Ue] rated operational voltage	600 V AC 250 V DC
Mounting mode	Unit mount
Poles description	3P
Short-circuit withstand	125 KA 240 V UL 489 100 KA 480 V UL 489 50 kA 600 V UL 489
Breaking capacity code	L
Electrical connection	Lugs line Lugs load
AWG gauge	AWG 14...AWG 3/0 aluminium/copper)
Terminal identifier	AL150HD
Magnetic tripping current	2250 A
Height	6.4 in (162.56 mm)
Width	2.12 in (53.85 mm)
Depth	4.36 in (110.74 mm)
Tightening torque	44.25 lbf.in (5 N.m) 0.00...0.15 in <sup>2</sup> (2.5...95 mm <sup>2</sup> ) (AWG 14...AWG 3/0)

### Environment

Product certifications	CE IEC CCC CSA NMX UL Listed
------------------------	---

### Ordering and shipping details

Category	01120 - HL,JL UNIT MT BREAKER/SWITCH
Discount Schedule	DE2
GTIN	00785901683186
Nbr. of units in pkg.	1
Package weight(Lbs)	4.61 lb(US) (2.09 kg)
Returnability	Yes
Country of origin	US

## Packing Units

Package 1 Height	5.80 in (14.732 cm)
Package 1 width	7.50 in (19.050 cm)
Package 1 Length	9.00 in (22.860 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
PVC free	Yes

## Contractual warranty

Warranty	18 months
----------	-----------