



Main

Product or component type	Additional I/O module
Range compatibility	Altivar Process ATV600 Altivar Machine ATV340 Altivar Process ATV900 Easy Altivar 610
Input/output type	2 analog input configurable voltage, current or probe 6 discrete input 2 discrete output
Analogue input number	2
Analogue input type	AI1, AI2 configurable current 0...20 mA/4...20 mA 0...1 ms 14 bits AI1, AI2 configurable voltage - 10...10 V DC, 24 V max 20 kOhm 0...1 ms 14 bits AI1, AI2 configurable PTC, Pt 100, Pt 1000 0...1 ms 14 bits
Discrete output number	2
Discrete output type	DQ11, DQ12) assignable logic 1 ms
Discrete output logic	DQ11, DQ12) negative DQ11, DQ12) positive
Discrete input number	6
Discrete input type	DI11...DI16) programmable 250 Ohm 1 ms
Discrete input logic	Negative DI11...DI16) Positive DI11...DI16)
Discrete input current	2.5 mA

Complementary

Discrete output voltage	24 V DC <= 30 V) assignable logic
Maximum output current	100 mA, assignable logic
Discrete input voltage	24 V DC <= 30 V)programmable
Electrical connection	Removable spring terminal block, 1.5 mm ² / AWG 16
Protection type	Reverse polarity protection digital input Short-circuit protection output
Net Weight	1.10 lb(US) (0.5 kg)

Ordering and shipping details

Category	22206 - ATV630 FRAMES 3 & 4
Discount Schedule	CP4E
GTIN	00785901969174
Nbr. of units in pkg.	1
Package weight(Lbs)	0.35 lb(US) (0.16 kg)
Returnability	Yes
Country of origin	ID

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.56 in (6.5 cm)
Package 1 width	5.12 in (13 cm)
Package 1 Length	7.48 in (19 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration