

# Product data sheet

## Characteristics

# QO130L125PQG

Load center, QO, 1 phase, 30 spaces, 34 circuits, 125A convertible main lugs, PoN, NEMA1, Qwik-grip, gnd bar, UL



### Main

Marketing Trade Name	QO
Product Type	Load Center
Provided Equipment	Qwik grip assembly kit 1)

### Complementary

Tightening Torque	Main lugs: 50 lb.in, AWG 6...AWG 2/0, aluminium/copper
Load Center Type	Main lugs
Rated Current	125 A
Number of Spaces	30
Max Short Circuit Current Rating	65 kA
Maximum Number of Single Pole Circuits	34
Maximum Number of Tandem Breakers	4
Number of Phases	1 phase
Voltage Rating	120/240 V AC
Wire Size	AWG 6...AWG 2/0 aluminium/copper
Ground Bar	Grounding bar included (not installed)
Busbar Material	Copper busbar
Enclosure Material	Welded sheet steel
Surface Finish	Baked enamel grey
Box Number	9Q
Height	29.84 in (758 mm)
Width	14.25 in (362 mm)

### Environment

Enclosure Rating	NEMA 1 for indoor
Ambient Air Temperature for Operation	23 °F (-5 °C) 104 °F (40 °C)
Product Certifications	UL Listed

### Ordering and shipping details

Category	10003 - QO PON 1PH LC,12-60 CKT, ML N1
Discount Schedule	DE3A
GTIN	00785901772606
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	Yes
Country of origin	US

## Packing Units

Package 1 Height	4.50 in (11.430 cm)
Package 1 width	14.70 in (37.338 cm)
Package 1 Length	31.70 in (80.518 cm)

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>