

# Pricing Guide

Data Security





# Why Choose Dahle?

**Need** - Recent events have made shredding confidential information a necessity. Documents found in the trash are not legally protected so they're fair game to individuals looking to find out more information about you and your business. This explains the rapid increase in identity theft and industrial espionage. Federal security laws require that medical and financial insti-

tutions as well as business owners must properly safeguard their client's personal information. What's the best way to dispose of this information? Shred it with a Dahle Professional Shredder.

**Quality** - Dahle shredders are carefully engineered in Germany by Novus Dahle GmbH using the latest technology and finest materials. Each component is man-

ufactured and assembled with precision from 90 years of experience. Dahle shredders feature cutting cylinders that are guaranteed to last a lifetime. Other components such as rubber shock mounts, electronic sensors, and a thermally protected motor produce a quality machine and peace of mind in knowing your Dahle shredder will provide many years of trouble-free operation.







## Number of Users

It's best to choose a shredder category based on the expected number of users. When making a selection, it's important to factor in anticipated company growth. While a certain size may satisfy your current needs, purchasing with the future in mind will benefit you in the long run.

|   |   |   |  |   |
|---|---|---|--|---|
|  |  |  |  |  |
| <b>Desktop</b><br>1-2 Users<br>Recommended  | <b>Small Office</b><br>1-3 Users<br>Recommended                                     | <b>Office</b><br>3-5 Users<br>Recommended   | <b>Department</b><br>5+ Users<br>Recommended   | <b>High Capacity</b><br>5+ Users<br>Recommended                                       |

## Security Levels

Under the international DIN 66399 standard, Dahle offers six security levels for document destruction. Each increase in security level represents a smaller particle (shred) size. A shredder with a greater security level will offer a lower sheet capacity compared to a lesser security model. Be sure to understand your company's security requirements before making a selection.

|   |  |  |
|---|--|--|
|  <b>P-2</b><br>For destruction of non-confidential documents |  <b>P-4 (most popular)</b><br>For destruction of sensitive & confidential documents |  <b>P-6</b><br>For destruction of highly secret documents   |
|  <b>P-3</b><br>For destruction of sensitive documents        |  <b>P-5</b><br>For destruction of secret documents                                  |  <b>P-7</b><br>NSA Approved for top-secret data destruction |




# Dahle Shredders


## Professional Shredders for Document Destruction

Secure information should never fall into the wrong hands. Dahle shredders are your best line of defense in preventing unauthorized access to secure information. Whether it's personal credit card statements or Top Secret government documents, Dahle has a shredder that will meet your needs.

### Security Levels



### Special Features





| Model | Security Level | Capacity #20 / #16 | Shred Size | Waste Volume | Feed Width | Speed feet/min | Decibel Level | Special Features |           | Features       |             |            | Staples /Clips | CDs DVDs | Warranty shredder   cylinders | Dimensions length x width x height | Weight | List Price |
|-------|----------------|--------------------|------------|--------------|------------|----------------|---------------|------------------|-----------|----------------|-------------|------------|----------------|----------|-------------------------------|------------------------------------|--------|------------|
|       |                |                    |            |              |            |                |               | Oil-Free         | CleanTEC® | Jam Protection | Smart Power | Auto Oiler |                |          |                               |                                    |        |            |

### Deskside Shredders (1-2 users)

|       |     |         |                 |        |        |        |       |          |   |   |   |   |   |                  |                            |        |       |
|-------|-----|---------|-----------------|--------|--------|--------|-------|----------|---|---|---|---|---|------------------|----------------------------|--------|-------|
| 22022 | P-4 | 7 / 9   | 3/16" x 1 3/16" | 4 gal. | 8 3/4" | 10 f/m | 59 dB | Oil-Free | . | . | . | . | . | 1 year   5 years | 7" x 12 1/2" x 15 1/2"     | 8 lbs  | \$149 |
| 22092 | P-4 | 10 / 12 | 3/16" x 1 3/16" | 4 gal. | 8 3/4" | 14 f/m | 62 dB | Oil-Free | . | . | . | . | . | 1 year   5 years | 7 3/4" x 12 1/4" x 16 1/2" | 14 lbs | \$229 |
| 22312 | P-4 | 15 / 17 | 3/16" x 1 7/16" | 7 gal. | 8 3/4" | 9 f/m  | 53 dB | Oil-Free | . | . | . | . | . | 1 year   5 years | 11" x 14 1/4" x 21"        | 24 lbs | \$399 |
| 22318 | P-4 | 16 / 18 | 3/16" x 1 1/8"  | 9 gal. | 8 3/4" | 11 f/m | 52 dB | Oil-Free | . | . | . | . | . | 1 year   5 years | 13" x 15 1/2" x 25 1/2"    | 32 lbs | \$519 |

### ShredMATIC® Auto-Feed Shredder (3-5 users)

|       |     |         |              |         |        |        |       |          |   |   |   |   |   |                  |                     |        |       |
|-------|-----|---------|--------------|---------|--------|--------|-------|----------|---|---|---|---|---|------------------|---------------------|--------|-------|
| 35314 | P-4 | 14 / 16 | 3/16" x 5/8" | 11 gal. | 8 3/4" | 12 f/m | 60 dB | Oil-Free | . | . | . | . | . | 1 year   5 years | 14" x 17" x 25 1/4" | 41 lbs | \$899 |
|-------|-----|---------|--------------|---------|--------|--------|-------|----------|---|---|---|---|---|------------------|---------------------|--------|-------|

### Small Office Shredders (1-3 users)

|       |     |         |                 |         |         |        |       |          |           |   |   |   |   |                    |                             |        |         |
|-------|-----|---------|-----------------|---------|---------|--------|-------|----------|-----------|---|---|---|---|--------------------|-----------------------------|--------|---------|
| 50114 | P-4 | 10 / 12 | 1/8" x 1 1/16"  | 8 gal.  | 9 1/2"  | 22 f/m | 44 dB | Oil-Free | .         | . | . | . | . | 2 years   Lifetime | 13 3/4" x 17" x 24 3/4"     | 46 lbs | \$950   |
| 50214 | P-4 | 10 / 12 | 1/8" x 1 1/16"  | 11 gal. | 9 1/2"  | 22 f/m | 46 dB | Oil-Free | .         | . | . | . | . | 2 years   Lifetime | 13 3/4" x 17" x 28"         | 50 lbs | \$1,200 |
| 51214 | P-4 | 10 / 12 | 1/8" x 1 1/16"  | 11 gal. | 9 1/2"  | 22 f/m | 46 dB | Oil-Free | CleanTEC® | . | . | . | . | 2 years   Lifetime | 13 3/4" x 17" x 28"         | 56 lbs | \$1,450 |
| 50310 | P-3 | 20 / 22 | 3/16" x 1 3/16" | 23 gal. | 10 1/4" | 20 f/m | 46 dB | Oil-Free | .         | . | . | . | . | 2 years   Lifetime | 17 1/4" x 21 1/2" x 34 1/4" | 95 lbs | \$1,550 |
| 50314 | P-4 | 16 / 18 | 1/8" x 1 3/16"  | 23 gal. | 10 1/4" | 20 f/m | 46 dB | Oil-Free | .         | . | . | . | . | 2 years   Lifetime | 17 1/4" x 21 1/2" x 34 1/4" | 89 lbs | \$1,750 |
| 51314 | P-4 | 16 / 18 | 1/8" x 1 3/16"  | 23 gal. | 10 1/4" | 18 f/m | 46 dB | Oil-Free | CleanTEC® | . | . | . | . | 2 years   Lifetime | 17 1/4" x 21 1/2" x 34 1/4" | 94 lbs | \$2,000 |
| 51322 | P-5 | 12 / 14 | 1/8" x 9/16"    | 23 gal. | 10 1/4" | 18 f/m | 46 dB |          | CleanTEC® | . | . | . | . | 2 years   Lifetime | 17 1/4" x 21 1/2" x 34 1/4" | 95 lbs | \$2,000 |
| 40330 | P-6 | 6 / 8   | 1/32" x 7/16"   | 23 gal. | 10 1/4" | 12 f/m | 47 dB |          | .         | . | . | . | . | 2 years   1 year   | 17 1/4" x 21 1/2" x 34 1/4" | 94 lbs | \$2,600 |

### Office Shredders (3-5 users)

|       |     |         |                 |         |         |        |       |          |           |   |   |   |   |                    |                             |         |         |
|-------|-----|---------|-----------------|---------|---------|--------|-------|----------|-----------|---|---|---|---|--------------------|-----------------------------|---------|---------|
| 40406 | P-2 | 30 / 34 | 1/4"            | 30 gal. | 10 1/4" | 22 f/m | 51 dB | Oil-Free | .         | . | . | . | . | 2 years   Lifetime | 17 1/4" x 21 1/2" x 36 3/4" | 97 lbs  | \$2,600 |
| 50410 | P-3 | 20 / 22 | 3/16" x 1 3/16" | 30 gal. | 10 1/4" | 20 f/m | 52 dB | Oil-Free | .         | . | . | . | . | 2 years   Lifetime | 17 1/4" x 21 1/2" x 36 3/4" | 98 lbs  | \$1,900 |
| 50414 | P-4 | 18 / 20 | 1/8" x 1 3/16"  | 30 gal. | 10 1/4" | 20 f/m | 46 dB | Oil-Free | .         | . | . | . | . | 2 years   Lifetime | 17 1/4" x 21 1/2" x 36 3/4" | 95 lbs  | \$2,400 |
| 51414 | P-4 | 18 / 20 | 1/8" x 1 3/16"  | 30 gal. | 10 1/4" | 18 f/m | 52 dB | Oil-Free | CleanTEC® | . | . | . | . | 2 years   Lifetime | 17 1/4" x 21 1/2" x 36 3/4" | 100 lbs | \$2,700 |
| 51422 | P-5 | 13 / 15 | 1/8" x 9/16"    | 30 gal. | 10 1/4" | 18 f/m | 53 dB |          | CleanTEC® | . | . | . | . | 2 years   Lifetime | 17 1/4" x 21 1/2" x 36 3/4" | 110 lbs | \$2,700 |
| 40430 | P-6 | 9 / 11  | 1/32" x 7/16"   | 30 gal. | 10 1/4" | 20 f/m | 52 dB |          | .         | . | . | . | . | 2 years   1 year   | 17 1/4" x 21 1/2" x 36 3/4" | 105 lbs | \$3,600 |
| 50464 | P-4 | 24 / 26 | 1/8" x 1 3/16"  | 30 gal. | 12"     | 20 f/m | 52 dB | Oil-Free | .         | . | . | . | . | 2 years   Lifetime | 17 1/4" x 21 1/2" x 36 3/4" | 119 lbs | \$2,800 |
| 51464 | P-4 | 24 / 26 | 1/8" x 1 3/16"  | 30 gal. | 12"     | 18 f/m | 52 dB | Oil-Free | CleanTEC® | . | . | . | . | 2 years   Lifetime | 17 1/4" x 21 1/2" x 36 3/4" | 118 lbs | \$3,100 |
| 51472 | P-5 | 16 / 18 | 1/8" x 9/16"    | 30 gal. | 12"     | 18 f/m | 53 dB |          | CleanTEC® | . | . | . | . | 2 years   Lifetime | 17 1/4" x 21 1/2" x 36 3/4" | 138 lbs | \$3,100 |

### Department Shredders (5+ users)

|       |     |         |                |         |     |        |       |          |           |   |   |   |   |                    |                     |         |         |
|-------|-----|---------|----------------|---------|-----|--------|-------|----------|-----------|---|---|---|---|--------------------|---------------------|---------|---------|
| 50514 | P-4 | 26 / 28 | 1/8" x 1 3/16" | 38 gal. | 12" | 16 f/m | 52 dB | Oil-Free | .         | . | . | . | . | 2 years   Lifetime | 20" x 29" x 34 1/2" | 141 lbs | \$3,100 |
| 51514 | P-4 | 26 / 28 | 1/8" x 1 3/16" | 38 gal. | 12" | 18 f/m | 52 dB | Oil-Free | CleanTEC® | . | . | . | . | 2 years   Lifetime | 20" x 29" x 34 1/2" | 143 lbs | \$3,400 |
| 51522 | P-5 | 16 / 18 | 1/8" x 9/16"   | 38 gal. | 12" | 18 f/m | 53 dB |          | CleanTEC® | . | . | . | . | 2 years   Lifetime | 20" x 29" x 34 1/2" | 154 lbs | \$3,400 |
| 40530 | P-6 | 10 / 12 | 1/32" x 7/16"  | 38 gal. | 12" | 15 f/m | 50 dB |          | .         | . | . | . | . | 2 years   1 year   | 20" x 29" x 34 1/2" | 146 lbs | \$4,300 |
| 40606 | P-2 | 36 / 40 | 1/4"           | 45 gal. | 16" | 26 f/m | 50 dB | Oil-Free | .         | . | . | . | . | 2 years   Lifetime | 20" x 29" x 38"     | 199 lbs | \$4,600 |
| 50564 | P-4 | 22 / 24 | 1/8" x 1 3/16" | 45 gal. | 16" | 30 f/m | 54 dB | Oil-Free | .         | . | . | . | . | 2 years   Lifetime | 20" x 29" x 38"     | 155 lbs | \$3,700 |
| 51564 | P-4 | 22 / 24 | 1/8" x 1 3/16" | 45 gal. | 16" | 20 f/m | 52 dB | Oil-Free | CleanTEC® | . | . | . | . | 2 years   Lifetime | 20" x 29" x 38"     | 158 lbs | \$4,100 |
| 51572 | P-5 | 14 / 16 | 1/8" x 9/16"   | 45 gal. | 16" | 20 f/m | 53 dB |          | CleanTEC® | . | . | . | . | 2 years   Lifetime | 20" x 29" x 38"     | 141 lbs | \$4,100 |

### High Capacity Shredders (5+ users)

|       |     |         |                |         |     |        |       |          |   |   |   |   |   |                    |                             |         |         |
|-------|-----|---------|----------------|---------|-----|--------|-------|----------|---|---|---|---|---|--------------------|-----------------------------|---------|---------|
| 20390 | P-2 | 55 / 60 | 1/4"           | 50 gal. | 16" | 22 f/m | 60 dB | Oil-Free | . | . | . | . | . | 2 years   Lifetime | 24 1/2" x 27 1/2" x 46 3/4" | 337 lbs | \$7,000 |
| 20396 | P-4 | 38 / 42 | 1/8" x 1 3/16" | 50 gal. | 16" | 22 f/m | 64 dB |          | . | . | . | . | . | 2 years   Lifetime | 24 1/2" x 29 1/2" x 46 3/4" | 359 lbs | \$8,200 |
| 20392 | P-5 | 26 / 28 | 1/8" x 9/16"   | 50 gal. | 16" | 22 f/m | 60 dB |          | . | . | . | . | . | 2 years   Lifetime | 24 1/2" x 29 1/2" x 46 3/4" | 359 lbs | \$8,200 |

### High Security Shredders (For Government Use)

|         |     |        |             |         |         |        |       |  |           |   |   |   |   |                  |                             |         |         |
|---------|-----|--------|-------------|---------|---------|--------|-------|--|-----------|---|---|---|---|------------------|-----------------------------|---------|---------|
| 20434ds | P-7 | 4 / 6  | 1mm x 4.7mm | 6 gal.  | 9 1/2"  | 13 f/m | 50 dB |  | .         | . | . | . | . | 2 years   1 year | 14" x 16" x 18"             | 66 lbs  | \$4,200 |
| 40334   | P-7 | 5 / 7  | 1mm x 4.7mm | 23 gal. | 10 1/4" | 22 f/m | 50 dB |  | .         | . | . | . | . | 2 years   1 year | 18 1/4" x 21 1/2" x 34 1/4" | 94 lbs  | \$3,100 |
| 41334   | P-7 | 5 / 7  | 1mm x 4.7mm | 23 gal. | 10 1/4" | 22 f/m | 50 dB |  | CleanTEC® | . | . | . | . | 2 years   1 year | 18 1/4" x 21 1/2" x 34 1/4" | 94 lbs  | \$3,400 |
| 40434   | P-7 | 8 / 10 | 1mm x 4.7mm | 30 gal. | 10 1/4" | 22 f/m | 52 dB |  | .         | . | . | . | . | 2 years   1 year | 18 1/4" x 21 1/2" x 36 3/4" | 105 lbs | \$4,500 |
| 41434   | P-7 | 8 / 10 | 1mm x 4.7mm | 30 gal. | 10 1/4" | 22 f/m | 52 dB |  | CleanTEC® | . | . | . | . | 2 years   1 year | 18 1/4" x 21 1/2" x 36 3/4" | 102 lbs | \$4,800 |
| 40534   | P-7 | 8 / 10 | 1mm x 4.7mm | 38 gal. | 12"     | 23 f/m | 52 dB |  | .         | . | . | . | . | 2 years   1 year | 21" x 29" x 34 1/2"         | 146 lbs | \$5,100 |
| 41534   | P-7 | 8 / 10 | 1mm x 4.7mm | 38 gal. | 12"     | 23 f/m | 52 dB |  | CleanTEC® | . | . | . | . | 2 years   1 year | 21" x 29" x 34 1/2"         | 146 lbs | \$5,500 |
| 20394   | P-7 | 9 / 11 | 1mm x 4.7mm | 50 gal. | 16"     | 35 f/m | 56 dB |  | .         | . | . | . | . | 2 years   1 year | 24 1/2" x 29 1/2" x 46 3/4" | 245 lbs | \$9,600 |

\*Sheet capacity will vary depending on paper size, weight, quality, and sufficient power.






# Dahle PowerTEC®


Industrial shredders for all media types

Shredding only paper is no longer enough. Sensitive information on digital devices is also a security risk. These ultra-powerful machines take data destruction to the next level by destroying paper and digital devices including hard drives, cell phones, SSD drives, and more.

## Media Types



## Special Features



## PowerTEC® 700 Series



### High Security Data Destruction

Dahle's PowerTEC® 700 Series shredders are NSA Approved for top-secret destruction of paper and optical media. They are precision engineered to support the high security shredding needs of military and government agencies.

## PowerTEC® 800 Series



### For Hard Drive | SSD | Cell Phone | Optical Media | Document Destruction

Dahle's PowerTEC® 800 Series shredders are the perfect machines for safely destroying paper and most forms of digital media. They are precision engineered to ensure your confidential data can never be seen again.

## PowerTEC® 900 Series



### High Volume Data Destruction

Dahle's PowerTEC® 900 Series Industrial Shredders are high capacity machines capable of destroying large volumes of sensitive information quickly. For added convenience, output conveyor belts are available to deliver shredded waste to a large recycling bin or baler.

## PowerTEC® Shredders

| Model  | Security Level | NSA Approved | Capacity #20 / #16 | Shred Size paper   media     | Waste Volume paper   media | Feed Width paper   media | Speed feet/min | Motor   | Decibel Level | Warranty machine   cylinders | Dimensions length x width x height | Weight    | Power Supply | List Price |
|--------|----------------|--------------|--------------------|------------------------------|----------------------------|--------------------------|----------------|---------|---------------|------------------------------|------------------------------------|-----------|--------------|------------|
| 707 PS | P-7            | Yes          | 11 / 13            | 1mm x 5mm                    | 53 gal.                    | 16"                      | 24 f/m         | 3.5 Hp  | 55 dB         | 2 years   1 year             | 21¾" x 28" x 43"                   | 320 lbs   | 115v         | \$11,000   |
| 717 OS | O-5            | Yes          | 1 disc             | 2mm x 4mm                    | 20 gal.                    | 5"                       | 9 f/m          | 2 Hp    | 55 dB         | 2 years   1 year             | 19¾" x 22¾" x 32¼"                 | 165 lbs   | 115v         | \$5,900    |
| 727 CS | P-7   O-5      | Yes          | 11 / 13            | 1mm x 5mm                    | 33 gal.   20 gal.          | 9"   5"                  | 24 f/m         | 3.5 Hp  | 55 dB         | 2 years   1 year             | 21¾" x 28" x 43"                   | 330 lbs   | 115v         | \$13,000   |
| 808 MS | O-3   E-3      |              | 1 drive            | 4mm x 15mm                   | 4 gal.                     | 6.5"                     |                | 3.5 Hp  | 55 dB         | 1 year                       | 21¾" x 21¾" x 39½"                 | 287 lbs   | 115v         | \$12,000   |
| 818 HD | H-3            | Yes          | 1 drive            |                              | 27 gal.                    | 4.7"                     |                | .75 Hp  | 60 dB         | 1 year                       | 19¾" x 20" x 34½"                  | 154 lbs   | 115v         | \$5,500    |
| 828 HD | H-4   P-3      |              | 100 / 110          | 5mm x 70mm<br>40mm x 40-90mm | 31 gal.   26 gal.          | 11.8"   4.7"             |                | 4.5 Hp  | 60 dB         | 1 year                       | 38¼" x 22½" x 46½"                 | 1,257 lbs | 220v 3 Phase | \$16,500   |
| 909 HS | P-3            |              | 85 / 90            | 4mm x 50mm                   | 68 gal.                    | 17.5"                    | 39 f/m         | 5 Hp    | 60 dB         | 1 year                       | 30" x 30" x 64¼"                   | 992 lbs   | 220v 3 Phase | \$14,500   |
| 919 IS | P-3            |              | 85 / 90            | 5mm x 40mm                   | 45 gal.                    | 16"                      | 39 f/m         | 5 Hp    | 65 dB         | 1 year                       | 52" x 47¼" x 48½"                  | 1,080 lbs | 220v 3 Phase | \$15,500   |
| 929 IS | P-3            |              | 500                | 8mm x 40mm                   | 120 gal.                   | 21.5"                    | 33 f/m         | 11.5 Hp | 70 dB         | 1 year                       | 78¾" x 48" x 64½"                  | 3,175 lbs | 220v 3 Phase | \$28,500   |
| 919 CB |                |              |                    |                              |                            | 16"                      | 49 f/m         |         | 65 dB         | 1 year                       | 92¼" x 25¾" x 50½"                 | 276 lbs   | 220v         | \$4,900    |
| 929 CB |                |              |                    |                              |                            | 21.5"                    | 49 f/m         |         | 65 dB         | 1 year                       | 83¼" x 30" x 46"                   | 276 lbs   | 220v         | \$5,200    |

## Shredder Supplies

| Model | Description                           | List Price | Model | Description                             | List Price | Model | Description                             | List Price |
|-------|---------------------------------------|------------|-------|---|------------|-------|---|------------|
| 20710 | DAHLE CleanTEC® Filter                | \$89       | 20723 | Shred Bags (200) - 8-10 gal. shredders  | \$110      | 20726 | Shred Bags (100) - 31-55 gal. shredders | \$140      |
| 20721 | Dahle Shredder Oil - 6-12 oz. bottles | \$70       | 20724 | Shred Bags (100) - 11-19 gal. shredders | \$110      | 20736 | Shred Bags (100) - 56-70 gal. shredders | \$300      |
| 20722 | Dahle Shredder Oil - 1-4 gal. bottles | \$200      | 20725 | Shred Bags (100) - 20-30 gal. shredders | \$130      | 20737 | Shred Bags (50) - 71-120 gal. shredders | \$320      |



Dahle North America, Inc.  
49 Vose Farm Road  
Peterborough, NH 03458  
Tel. (800) 995-1379  
info@dahle.com



www.dahle.com

A company of the emco Group

