

Product data sheet

Characteristics

QO142M200PQCVP

Load center, QO, 1 phase, 42 spaces, 52 circuits, 200A convertible main breaker, PoN, NEMA1, Qwik-grip, value pack



Main

Marketing Trade Name	QO
Product Type	Load Center value pack
Cover Type	Combination flush/surface cover
Provided Equipment	Circuit breaker 3) 1P 20 A 120 V AC downstream Circuit breaker 2) 2P 30 A 120/240 V AC downstream Load center 1) 42P 200 A 120/240 V AC Circuit breaker 1) 125 A 120/240 V AC main supply ready assembled Qwik grip assembly kit 1)

Complementary

Tightening Torque	Cover: 20 lb.in
Load Center Type	Main breaker
Rated Current	200 A
Number of Spaces	42
Max Short Circuit Current Rating	22 kA
Maximum Number of Single Pole Circuits	52
Maximum Number of Tandem Breakers	0
Number of Phases	1 phase
Voltage Rating	120/240 V AC
Wire Size	AWG 4...300 kcmil aluminium/copper
Ground Bar	Grounding bar (ordered separately)
Busbar Material	Copper busbar
Enclosure Material	Welded sheet steel
Surface Finish	Baked enamel grey
Box Number	11Q
Height	39.37 in (1000 mm)
Width	14.25 in (362 mm)
Depth	3.74 in (95 mm)

Environment

Enclosure Rating	NEMA 1 for indoor
Ambient Air Temperature for Operation	23 °F (-5 °C) 104 °F (40 °C)
Product Certifications	UL Listed

Ordering and shipping details

Category	00184 - MISC. QO 1PH LOAD CENTERS
Discount Schedule	DE3A
GTIN	00785901634676
Nbr. of units in pkg.	1
Package weight(Lbs)	38.4 lb(US) (17.42 kg)
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Unit Type of Package 2	PAL
Number of Units in Package 2	18
Package 2 Weight	717.00 lb(US) (325.225 kg)
Package 2 Height	37.80 in (96.012 cm)
Package 2 width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration