

High Performance Masking Tape

2693

Technical Data

February, 2011

Product Description

Scotch® High Performance Masking Tape 2693 is a smooth, heavy duty, mini-crepe paper masking tape suitable for most paint masking applications. Designed for automotive, truck and bus applications where very aggressive room temperature and high temperature holding is required.

Product Construction

Backing	Adhesive	Color	Standard Roll Length
Smooth mini-crepe paper treated with a heat resistant saturant	Synthetic rubber	Tan	55 m (60.17 yds.)*

*Available in metric widths (eg, 24 mm corresponds to 1 inch).

Typical Physical Properties

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

		ASTM Test Method
Adhesion to Steel:	40 oz./in. width (44 N/100 mm)	D-3330
Tensile Strength:	29 lbs./in. width (515 N/100 mm)	D-3759
Elongation at Break:	10%	D-3759
Tape Thickness:	7.9 mils (0.20 mm)	D-3652
Temperature Use Range:	Up to 325°F (163°C) for 30 minutes	

Features

- Offers excellent paint masking performance with high solids paints and urethane clear coats used in the transportation industry.
- Holding power resists the most stringent applications and bake cycles.
- Can be removed warm or cold from most surfaces without adhesive transfer.
- Has been laboratory tested on painted steel panels and found to remove cleanly at bake temperatures up to 325°F (163°C) for 30 minutes. The actual temperature and time performance may be higher or lower for a given application. Clean removal can vary dependent on surface type, processing conditions such as multiple bakes, type of paint involved as well as the temperature of the surface at removal. We recommend testing the product under your conditions to determine your performance limits.
- Excellent conformability and tear properties.
- Smoothness of the backing makes this tape very “user friendly.”
- Excellent paint flake resistance.
- Balanced construction with a stronger backing gives this tape easy removal properties without slivering.
- Good resistance to adhesive transfer on automotive type rubber moldings when removed at room temperatures.
- Should not be subjected to outdoor exposure or prolonged exposure to sunlight as tape may become difficult to remove.

Scotch® High Performance Masking Tape

2693

Storage	Store under normal conditions of 70°F (21°C) and 50% R.H. in the original carton.
Shelf Life	To obtain best performance, use this product within one year from date of manufacture.
Technical Information	The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.
Product Use	Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.
Warranty, Limited Remedy, and Disclaimer	Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.
Limitation of Liability	Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

ISO 9001:2008

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001:2008 standards.



Industrial Adhesives and Tapes Division

3M Center, Building 225-3S-06
St. Paul, MN 55144-1000
800-362-3550 • 877-369-2923 (Fax)
www.3M.com/industrial



Recycled Paper
40% pre-consumer
10% post-consumer

Scotch is a registered trademark of 3M.
Printed in U.S.A.
©3M 2011 70070944130 (2/11)