



**Bullet Network Camera** 



2MP 60 fps • SNV II • WDR Pro II • Remote Focus • Smart Stream III • Smart IR II • 50M IR • IP66 • IP67 • IK10

The IB9365 series is the new flagship outdoor bullet network camera from VIVOTEK, equipped with a full HD sensor capable of 1920x1080 resolution at 60 fps. With the most updated VIVOTEK SNV and WDR Pro technology, the IB9365 series is capable of capturing the highest quality images in both low light and high contrast environments.


The IB9365 series also offers the best in night time surveillance technology. By adopting Smart IR II technology from VIVOTEK speed domes, the IB9365 IR illuminators now align with the remote focus lens' focus angle to provide the best IR image quality at any lens setting. This feature optimizes IR intensity, reduces IR hotspots, and increases the IR effective range up to 50 meters.


Additionally, the IB9365 series employs VIVOTEK's Smart Stream III technology and H.265 compression codec, reducing bandwidth more than 90%\* while still maintaining excellent image quality compared to traditional H.264 without smart streaming. Furthermore, the VIVOTEK VADP (VIVOTEK Application Development Platform) allows users to add customized programs for various applications and user scenarios. Protecting all these features is the IB9365's IP66, IP67 and IK10 rated housing, capable of operating from -50°C to 50°C (IB9365-EHT).

\* Depending on scenes

### **Key Features**

- · 60 fps @ 1920x1080
- · H.265 Compression Technology
- · 4 ~ 9 mm, Remote Focus, P-iris Lens
- · Smart Stream III to Optimize Bandwidth Efficiency
- · SNV II (Supreme Night Visibility) for Low Light Conditions
- WDR Pro II (140dB) to Provide Extreme Visibility in Extremely Bright or Dark Environments
- · Built-in IR Illuminators, Effective up to 50 Meters
- · Smart IR II Technology to Avoid Overexposure
- · Smart Motion Detection to Reduce False Alarms
- Trend Micro IoT Security within Standard Warranty Period
- Weather-proof IP66, IP67 and Vandal-proof IK10-rated Housing
- $\cdot$  -50°C  $\sim$  50°C Wide Temperature Range for Extreme Weather Conditions (IB9365-EHT)






# **Technical Specifications**

| -                                |   |                        |   |
|----------------------------------|---|------------------------|---|
| Model                            | IB9365-HT:<br>Vari-focal, Remote Focus<br>IB9365-EHT:<br>Vari-focal, Remote Focus, -50°C ~ 50°C   | Audio                  |   |
|                                  |   | Audio Capability       | Two-way audio   |
| System Information               |   | Compression            | G.711, G.726  |
| CPU                              | Multimedia SoC (System-on-Chip)   | Interface              | External Mic input<br>External line output  |
| Flash                            | 128MB   | Network                |   |
| RAM                              | 512MB   | Users                  | Live viewing for up to 10 clients   |
| Camera Features                  |   |                        | IPv4, IPv6, TCP/IP, HTTP, HTTPS, UPnP, RTSP/  |
| Image Sensor                     | 1/2" Progressive CMOS   | Protocols              | RTP/RTCP, IGMP, CIFS/SMB, SMTP, FTP, DHCP, NTP, DNS, DDNS, PPPOE, COS, QOS, SNMP, 802.1X, UDP, ICMP, ARP, SSL/TLS   |
| Maximum Resolution               | 1920x1080   | Interface              | 10 Base-T/100 Base-TX Ethernet (RJ-45) *It is highly recommended to use standard CAT5e & CAT6 cables which are compliant  |
| Lens Type                        | Vari-focal, Remote Focus  |                        |   |
| Focal Length                     | $f = 4 \sim 9$ mm $f = 3.5 \sim 11.4$ mm (equivalent focal length @ 1/2.8")   | ONVIF                  | with the 3P/ETL standard.  Supported, specification available at www.onvif.org  |
| Aperture                         | F1.3 ~ F2.2   | Intelligent Video      | <u> </u>  |
| Auto-iris                        | P-iris  |                        | Five-window video motion detection,   |
| Field of View                    | 46° ~ 100° (Horizontal)<br>26° ~ 52° (Vertical)   | Smart Motion Detection | human detection, time filter  |
|                                  | 53° ~ 120° (Diagonal)   | Alarm and Event        |   |
| Shutter Time                     | 1/5 sec. to 1/32,000 sec.   | Alarm Triggers         | Motion detection, manual trigger, digital input, periodical trigger, system boot, recording notification, camera tampering detection, audio detection, MicroSD card life expectancy |
| WDR Technology                   | WDR Pro II  |                        |   |
| Day/Night                        | Removable IR-cut filter for day & night function  | Alarm Events           | Event notification using digital output, HTTP,<br>SMTP, FTP, NAS server and MicroSD card<br>File upload via HTTP, SMTP, FTP, NAS server<br>and MicroSD card                         |
| Minimum Illumination             | 0.04 Lux @ F1.3 (Color), 50IRE<br>0.002 Lux @ F1.3 (Color), 30IRE<br>0 Lux with IR illumination on  |                        |   |
| Tilt Range                       | 90°   | General                |   |
| Rotation Range                   | 180°  | Connectors             | RJ-45 cable connector for Network/PoE connection Audio line in Audio line out AC 24 V DC 12 V Digital input *2 Digital output *2 BNC out  |
| Pan/Tilt/Zoom<br>Functionalities | ePTZ:48x digital zoom<br>(4x on IE plug-in, 12x built in)   |                        |   |
| IR Illuminators                  | Built-in IR illuminators, effective up to 50 meters with Smart IR II, IR LED*5  |                        |   |
| On-board Storage                 | Slot type: MicroSD/SDHC/SDXC card slot<br>Seamless Recording  | LED Indicator          | System power and status indicator   |
| Video                            |   | Power Input            | IB9365-HT:<br>AC 24V, DC 12V, IEEE 802.3af PoE Class 0<br>IB9365-EHT:<br>AC 24V, DC 12V, IEEE 802.3at PoE Class 4   |
| Compression                      | H.265, H.264, MJPEG   |                        |   |
| Maximum Frame Rate               | 60 fps @ 1920x1080  | Power Consumption      | IB9365-HT: Max. 11.9 W  |
| Maximum Streams                  | 4 simultaneous streams  | Tower Consumption      | IB9365-EHT: Max. 24.8 W   |
| S/N Ratio                        | 66 dB   | Dimensions             | Ø 121 x 121 x 415 mm (w/ junction box)<br>Ø 121 x 121 x 351 mm (w/o junction box)   |
| Dynamic Range                    | 140 dB  | Weight                 | 1,942 g (w/ junction box)<br>1,475 g (w/o junction box)   |
| Video Streaming                  | Adjustable resolution, quality and constant bit rate control, Smart Stream III  | Casing                 | IP66, IP67, IK10(Metal Housing)   |
| Image Settings                   | Time stamp, text overlay, flip & mirror;<br>Configurable brightness, contrast,<br>saturation, sharpness, white balance,<br>exposure control, gain, backlight<br>compensation, privacy masks; Scheduled<br>profile settings, video rotation, 3DNR, DIS,<br>HLC | Safety Certifications  | CE, LVD, FCC Class A, VCCI, C-Tick, UL  |
|                                  |   |                        |   |
|                                  |   |                        |   |

## **Technical Specifications**

IB9365-HT: Starting Temperature: -10°C ~ 50°C (14°F ~ 122°F) Working Temperature: -30°C ~ 50°C (-22°F ~ 122°F) IB9365-EHT: Operating Temperature Starting Temperature: -40°C ~ 50°C (-40°F ~ 122°F) Working Temperature: -50°C ~ 50°C (-58°F ~ 122°F) Humidity 90% Warranty 36 months **System Requirements** Microsoft Windows 8/7 Operating System Mozilla Firefox 7~43 (streaming only) Web Browser Internet Explorer 10/11

### **Dimensions**



# Included Accessories

Other Players

Others Quick installation guide, warranty card, screw pack, alignment sticker, junction box

VLC: 1.1.11 or above

Quicktime: 7 or above

## **Compatible Accessories**

#### **Mounting Kits**



AM-719
Junction Box (Standard Package)



AM-312 Pole Mount Adapter



AM-412 Corner Mount Adapter

