

Product data sheet

Characteristics

QOE250GF1NM

Load center, QO, 1 phase, 50A enclosed main breaker, NEMA3R, ground fault protection, nonmetallic, spa



Main

Marketing Trade Name	QO
Product Type	Load Center
Enclosure Type	Weatherproof enclosure

Complementary

Load Center Type	Main breaker
Rated Current	50 A
Number of Spaces	2
Max Short Circuit Current Rating	10 kA
Number of Phases	1 phase
Voltage Rating	120/240 V AC
Ground Bar	Grounding bar (factory installed)
Electrical Connection	Lugs
Wiring Configuration	3-wire
Enclosure Material	Non-metallic
Surface Finish	Baked enamel Gray
Box Number	1NM
Height	9.17 in (233 mm)
Width	6.54 in (166 mm)
Depth	3.90 in (99 mm)

Environment

Enclosure Rating	NEMA 3R outdoor
Product Certifications	UL Listed

Ordering and shipping details

Category	00167 - DE3A MISC
Discount Schedule	DE3A
GTIN	00785901389507
Nbr. of units in pkg.	1
Package weight(Lbs)	2.4 lb(US) (1.09 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	4.00 in (10.16 cm)
Package 1 width	6.80 in (17.272 cm)
Package 1 Length	9.50 in (24.13 cm)
Unit Type of Package 2	CAR
Number of Units in Package 2	10
Package 2 Weight	24.90 lb(US) (11.294 kg)
Package 2 Height	10.60 in (26.924 cm)
Package 2 width	13.20 in (33.528 cm)
Package 2 Length	20.30 in (51.562 cm)
Unit Type of Package 3	PAL
Number of Units in Package 3	240
Package 3 Weight	645.00 lb(US) (292.567 kg)
Package 3 Height	46.50 in (118.11 cm)
Package 3 width	40.00 in (101.6 cm)
Package 3 Length	48.00 in (121.92 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------