# Product data sheet Characteristics

# RXG11B7

Harmony, Interface plug-in relay, 10 A, 1 CO, with lockable test button, 24 V AC





Main	
Range of product	Harmony Electromechanical Relays
Series name	Interface relay
Product or component type	Plug-in relay
Device short name	RXG
Contacts type and composition	1 C/O

### Complementary

Status LED	Without
Contacts material	Silver alloy (AgSnO2In2O3)
Maximum contact resistance	100 mOhm
[Ithe] conventional enclosed thermal current	10 A -40131 °F (-4055 °C)
[le] rated operational current	10 A 30 V DC) UL 10 A 30 V DC) IEC 10 A 250 V AC) IEC 10 A 250 V AC) UL
Maximum switching voltage	250 V AC 30 V DC
Load current	10 A 250 V AC
Maximum switching capacity	2500 VA
Minimum switching capacity	500 mW at 100 mA, 5 V DC
Operating rate	<= 1800 cycles/hour under load <= 18000 cycles/hour no-load
Utilisation coefficient	20 %
Mechanical durability	10000000 cycles
Electrical durability	100000 Cycles NO resistive at 55 °C 100000 cycles NC resistive at 55 °C
[Ui] rated insulation voltage	250 V IEC 300 V CSA 300 V UL
[Uimp] rated impulse withstand voltage	6 kV 1.2/50 µs
Dielectric strength	1000 V AC between contacts with micro disconnection 5000 V AC between coil and contact with reinforced insulation
Coil resistance	260 Ohm +/- 10 %
Insulation resistance	1000 MOhm at 500 V DC
Test levels	Level A
Mounting position	Any position
Average consumption in VA	0.82 VA 60 Hz
Drop-out voltage threshold	>= 0.3 Uc AC
Control circuit voltage limits	0.81.1 Uc AC
Coil insulation class	Class F
Operate time	20 ms
Release time	20 ms
[Uc] control circuit voltage	24 V AC 50/60 Hz

Safety reliability data	B10d = 100000	
Colour of cover	Standard	
Control type	Lockable test button	
Local signalling	Flag	
Torque value	7.08 lbf.in (0.8 N.m)	
Net Weight	0.04 lb(US) (0.02 kg)	
Device presentation	Complete product	

### Environment

Z. T. T. G. T. T. G. T.	
Vibration resistance	3 gn +/- 0.75 mm 10150 Hz)in operation 5 gn +/- 0.75 mm 10150 Hz)not in operation
IP degree of protection	IP40
Shock resistance	20 gn in operation 100 gn not in operation
Protection category	RTI
Standards	CSA C22.2 No 14 UL 508 IEC 61810-1
Product certifications	CE UL EAC CSA DNV-GL
Pollution degree	2
Overvoltage category	III
Ambient air temperature for storage	-40185 °F (-4085 °C)
Ambient air temperature for operation	-40158 °F (-4070 °C)
Relative humidity	1085 %
	<del></del>

# Ordering and shipping details

000
CP2
00785901949701
10
10 lb(US) (4.54 kg)
No
CN


# Packing Units


Package 1 Height	1.40 in (35.500 mm)
Package 1 width	0.51 in (13.000 mm)
Package 1 Length	1.14 in (29.000 mm)


# Offer Sustainability

Green Premium product
WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
Yes
Pro-active compliance (Product out of EU RoHS legal scope)
Yes
Yes
₽¥Yes
China RoHS Declaration
Product Environmental Profile

### **Dimensions**









# RXG11B7

## Wiring Diagram



#### Performance Curves

### Maximum Switching Capacity



X : Switching voltage (V)

Y: Switching current (A)

(1) AC Resistive Load


(2) AC Inductive Load cos(Ø)=0.4

(3) DC Resistive Load

(4) DC Inductive Load (L/R=7ms)

#### Life Expectancy

#### Resistive Load




X : Contact Current (A)

Y : Operating Cycle Number

#### Life Expectancy

#### Inductive Load




X : Contact Current (A)

Y: Operating Cycle Number

NOTE: These are typical curves, actual durability depends on load, environment, duty cycle, etc.

### Coil Operating Range

### AC Coil Operating Range VS Ambient Temperature



X : Ambient temperature (°C)

Y : Coil voltage (U/Uc)

(1) Permitted operating range area