

LC1D40B7

IEC contactor, TeSys D, nonreversing, 40A, 30HP at 480VAC, up to 100kA SCCR, 3 phase, 3 NO, 24VAC 50/60Hz coil, open



Main

Range of product	TeSys D
Range	TeSys
Product or component type	Contactors
Device short name	LC1D
Contactors application	Motor control Resistive load
Utilisation category	AC-3 AC-4 AC-2 AC-1
Control circuit type	AC at 50/60 Hz
Poles description	3P
Pole contact composition	3 NO
[Ie] rated operational current	40 A 140 °F (60 °C)) <= 440 V AC AC-3 power circuit 60 A 140 °F (60 °C)) <= 440 V AC AC-1 power circuit
Motor power kW	18.5 KW 380...400 V AC 50 Hz AC-3) 22 KW 500 V AC 50 Hz AC-3) 30 KW 660...690 V AC 50 Hz AC-3) 22 KW 1000 V AC 50 Hz AC-3) 22 KW 415 V AC 50 Hz AC-3) 22 KW 440 V AC 50 Hz AC-3) 11 KW 220...230 V AC 50 Hz AC-3) 9 kW 400 V AC 50 Hz AC-4)

Complementary

Coil technology	Without built-in bidirectional peak limiting diode suppressor
Front cover	With
Maximum Horse Power Rating	3 Hp 115 V at AC 60 Hz for 1 phase 5 Hp 230/240 V at AC 60 Hz for 1 phase 10 Hp 200/208 V at AC 60 Hz for 3 phase 10 Hp 230/240 V at AC 60 Hz for 3 phase 30 Hp 460/480 V at AC 60 Hz for 3 phase 30 hp 575/600 V at AC 60 Hz for 3 phase
Auxiliary contacts type	Type mechanically linked 1 NO + 1 NC conforming to IEC 60947-5-1 Type mirror contact 1 NC conforming to IEC 60947-4-1
Auxiliary contact composition	1 NO + 1 NC
[Uc] control circuit voltage	24 V AC 50/60 Hz
[Ui] rated insulation voltage	Control circuit 600 V CSA Control circuit 600 V UL Power circuit 600 V CSA Power circuit 600 V UL Control circuit 690 V IEC 60947-1 Power circuit 690 V IEC 60947-1
[Uimp] rated impulse withstand voltage	8 kV IEC 60947
Overvoltage category	III
Mounting support	Rail Plate
Flame retardance	V1 conforming to UL 94

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Connections - terminals	Control circuit screw clamp terminals 1 0.00...0.01 in ² (1...4 mm ²)rigid Control circuit screw clamp terminals 2 0.00...0.01 in ² (1...4 mm ²)rigid Control circuit screw clamp terminals 1 0.00...0.01 in ² (1...4 mm ²)flexible without cable end Control circuit screw clamp terminals 2 0.00...0.01 in ² (1...4 mm ²)flexible without cable end Control circuit screw clamp terminals 1 0.00...0.00 in ² (1...2.5 mm ²)flexible with cable end Control circuit screw clamp terminals 2 0.00...0.00 in ² (1...2.5 mm ²)flexible with cable end Power circuit screw terminals 1 0.00...0.04 in ² (2.5...25 mm ²)rigid Power circuit screw terminals 2 0.00...0.02 in ² (2.5...16 mm ²)rigid Power circuit screw terminals 1 0.00...0.04 in ² (2.5...25 mm ²)flexible without cable end Power circuit screw terminals 2 0.00...0.02 in ² (2.5...16 mm ²)flexible without cable end Power circuit screw terminals 1 0.00...0.04 in ² (2.5...25 mm ²)flexible with cable end Power circuit screw terminals 2 0.00...0.02 in ² (2.5...10 mm ²)flexible with cable end
Tightening torque	Control circuit 10.62 lbf.in (1.2 N.m) screw clamp terminal flat Ø 6 mm Control circuit 10.62 lbf.in (1.2 N.m) screw clamp terminal Philips No 2 Power circuit 44.25 lbf.in (5 N.m) screw terminal flat Ø 6 to Ø 8 mm
[Ue] rated operational voltage	Power circuit: <= 690 V AC 25...400 Hz
[Ith] conventional free air thermal current	10 A 140 °F (60 °C) control circuit 60 A 140 °F (60 °C) power circuit
Irms rated making capacity	800 A 440 V power circuit IEC 60947 140 A AC control circuit IEC 60947-5-1
Rated breaking capacity	800 A 440 V power circuit IEC 60947
Associated fuse rating	10 A gG control circuit IEC 60947-5-1 80 A gG <= 690 V type 1 power circuit 80 A gG <= 690 V type 2 power circuit
Power dissipation per pole	5.4 W AC-1 2.4 W AC-3
Inrush power in VA	140 VA 0.75 68 °F (20 °C)) 160 VA 0.75 68 °F (20 °C))
Hold-in power consumption in VA	13 VA 60 Hz 0.3 68 °F (20 °C)) 15 VA 50 Hz 0.3 68 °F (20 °C))
Operating time	4...19 ms opening 12...26 ms closing
Safety reliability level	B10d = 1369863 cycles contactor with nominal load EN/ISO 13849-1 B10d = 2000000 cycles contactor with mechanical load EN/ISO 13849-1
Mechanical durability	6000000 cycles
Maximum operating rate	3600 cyc/h 60 °C
Minimum switching current	5 mA control circuit
Minimum switching voltage	17 V control circuit
Non-overlap time	1.5 Ms on de-energisation between NC and NO contacts 1.5 ms on energisation between NC and NO contacts
Insulation resistance	> 10 MOhm control circuit
Height	5.00 in (127 mm)
Width	2.95 in (75 mm)
Depth	4.69 in (119 mm)
Net Weight	3.09 lb(US) (1.4 kg)

Environment

Standards	EN 60947-5-1 IEC 60947-5-1 EN 60947-4-1 IEC 60947-4-1 CSA C22.2 No 14 UL 508
Product certifications	LROS (Lloyds register of shipping) DNV RINA CSA GL UL CCC BV GOST
IP degree of protection	IP2x IEC 60529 IP2x VDE 0106
Ambient air temperature for storage	-76...176 °F (-60...80 °C)
Operating altitude	3000 m without derating
Fire resistance	1562 °F (850 °C) IEC 60695-2-1
Shock resistance	10 gn contactor opened 15 gn contactor closed
Vibration resistance	2 gn 5...300 Hz contactor opened 4 gn 5...300 Hz contactor closed
Heat dissipation	4...5 W 50/60 Hz control circuit

Ordering and shipping details

Category	22357 - CTR, TESYS D, OPEN, 40-65A AC
Discount Schedule	I12
GTIN	00785901207610
Nbr. of units in pkg.	1
Package weight(Lbs)	3.19 lb(US) (1.45 kg)
Returnability	Yes
Country of origin	CZ

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	3.74 in (9.5 cm)
Package 1 width	5.24 in (13.3 cm)
Package 1 Length	5.51 in (14 cm)
Unit Type of Package 2	S02
Number of Units in Package 2	5
Package 2 Weight	16.54 lb(US) (7.504 kg)
Package 2 Height	5.91 in (15 cm)
Package 2 width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)
Unit Type of Package 3	P06
Number of Units in Package 3	80
Package 3 Weight	284.00 lb(US) (128.82 kg)
Package 3 Height	30.31 in (77 cm)
Package 3 width	31.50 in (80 cm)
Package 3 Length	23.62 in (60 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------