

Convoy Medium Duty Natural

MEDIUM DUTY PAPER TAPE

DESCRIPTION

Natural kraft carton sealing tape manufactured with standard water-activated adhesive.

PRODUCT APPLICATION

Recommended for inner carton sealing or for lightweight cartons that will be shipped in unitized loads or full pallets.

STORAGE RECOMMENDATION

Store new stock behind current stock. Store in a clean, dry place. Temperature of 70°F (21°C) +/- 6°F, and 40% to 50% relative humidity are recommended.

SHELF LIFE

When stored under recommended conditions, converted rolls have an expected shelf life of up to two years from date of shipment. Jumbo rolls have the same expected shelf life, but it is recommended that they are converted within 6 months of date of shipment.



100 Paramount Drive, Suite 300 | Sarasota, FL 34232 | USA
Customer Service: 800.IPG.8273 | 800.474.8273
Tape Technical Service: 877.447.4832
www.itape.com | info@itape.com

While we believe them to be reliable, the statements and information herein are only for general guidance and are not warrants or guarantees for accuracy and completeness. The user must, by test or otherwise, determine suitability for this purpose. There is no warranty of fitness for a particular purpose. Our standard term and conditions of sale apply exclusively to all orders, and all liability for damages of any kind, including consequential, exceeding purchase price is excluded. No one is authorized by us to make oral warranties. We reserve the right to make changes without notice or obligation in our products and publications.

EFFECTIVE: 06/21

INTERTAPE POLYMER GROUP® TECHNICAL DATA SHEET

CONSTRUCTION PER 3,000 SQUARE FEET (metric)

Paper	57 lb (93 g/m ²) Natural Kraft Paper
Water-Activated Adhesive	Chemically Grafted Starch Based Copolymer, Designated as S3911

PHYSICAL PROPERTIES

Caliper	5.6 mils (0.14mm)
MD Tensile	45 lbs/in (197 N/25mm)
CD Tensile	23 lbs/in (101 N/25mm)

ADHESION (WATER AT RECOMMENDED 110°F/43°C)

Fipago	
2/0	23
2/1	42
5/0	48
15/0	82
McLaurin	34



Convoy Medium Duty White

MEDIUM DUTY PAPER TAPE

DESCRIPTION

Bleached kraft carton sealing tape manufactured with water-activated adhesive.

PRODUCT APPLICATION

Recommended for inner carton sealing or for lightweight cartons that will be shipped in unitized loads or full pallets.

STORAGE RECOMMENDATION

Store new stock behind current stock. Store in a clean, dry place. Temperature of 70°F (21°C) +/- 6°F, and 40% to 50% relative humidity are recommended.

SHELF LIFE

When stored under recommended conditions, converted rolls have an expected shelf life of up to two years from date of shipment. Jumbo rolls have the same expected shelf life, but it is recommended that they are converted within 6 months of date of shipment.



100 Paramount Drive, Suite 300 | Sarasota, FL 34232 | USA
Customer Service: 800.IPG.8273 | 800.474.8273
Tape Technical Service: 877.447.4832
www.itape.com | info@itape.com

While we believe them to be reliable, the statements and information herein are only for general guidance and are not warrants or guarantees for accuracy and completeness. The user must, by test or otherwise, determine suitability for this purpose. There is no warranty of fitness for a particular purpose. Our standard term and conditions of sale apply exclusively to all orders, and all liability for damages of any kind, including consequential, exceeding purchase price is excluded. No one is authorized by us to make oral warranties. We reserve the right to make changes without notice or obligation in our products and publications.

EFFECTIVE: 06/21

INTERTAPE POLYMER GROUP® TECHNICAL DATA SHEET

CONSTRUCTION PER 3,000 SQUARE FEET (metric)

Paper	55 lb. (90 g/m ²) Bleached Kraft Paper (virgin fibers)
Water-Activated Adhesive	Chemically Grafted Starch Based Copolymer, Designated as S3911

PHYSICAL PROPERTIES

Caliper	5.2 mils (0.13mm)
MD Tensile	57 lbs/in (250 N/25mm)
CD Tensile	26 lbs/in (114 N/25mm)

ADHESION (WATER AT RECOMMENDED 110°F/43°C)

Fipago	
2/0	20
2/1	40
5/0	46
15/0	84
McLaurin	34

