



Main

Range	Spacial
Product name	Spacial SM
Product or component type	Compact enclosure
Application	Multi-purpose
Installation accessory type	Floor-standing
Device composition	1 body 1 cable gland plate 1 locking system with handle door 4 mounting plate bracket 1 mounting plate 1 door
Removable parts	Door by screws hinge Mounting plate by screws mounting plate bracket Mounting plate bracket by screws
Enclosure nominal height	78.74 in (2000 mm)
Enclosure nominal width	31.50 in (800 mm)
Enclosure nominal depth	19.69 in (500 mm)

Complementary

Number of doors	Front 1
Door opening side	Reversible 120 °)
Door type	Solid
Lock type	4 points lock, handle with 5 mm double bar insert
Body type	Single piece body with welded rear panel Front part forming a rigid frame with welded corners
Mounting plate description	Plain
Type of gland plate	Standard
Cable entry	1 entry
Material	Mounting plate galvanised steel Body sheet steel Door sheet steel Hinge: zamak
Surface finish	Epoxy-polyester powder
Color	Enclosure Gray RAL 7035) Handle: black (RAL 9005)
Accessibility for operation	Front
Net Weight	308.65 lb(US) (140 kg)

Environment

Standards	IEC 62208
Product certifications	BV UL DNV
IK degree of protection	IK10 conforming to IEC 62262
IP degree of protection	IP55 IEC 60529

Ordering and shipping details

Category	80035 - ENCLOSURE SYSTEMS FLOOR MOUNT
Discount Schedule	ES1
GTIN	00785901506553
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No
Country of origin	ES

Packing Units

Package 1 Height	83.86 in (2130.000 mm)
Package 1 width	33.27 in (845.000 mm)
Package 1 Length	23.23 in (590.000 mm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------