



Screw Selection Guide

Head Types *(measure length from surface of material to screw tip)*



Head Sizes

	#4	#5	#6	#7	#8	#9	#10	#14
Flat Head	0.225"	0.252"	0.255"	0.295"	0.332"	0.335"	0.385"	0.491"
Oval Head		0.252"						
Pan Head			0.270"	0.296"	0.322"		0.373"	
Pocket Hole/Face Frame			Modified	Modified				
Truss Head			0.260"		0.384"			
Standard Washer Head					0.375"		0.500"	
Large Washer Head					0.500"			



Drives



PHILLIPS

Most common in wood applications



PHILLIPS SLOTTED COMBO

Popular on truss head machine screws

Use Phillips bit to drive

Use Phillips or Flat bit to remove



POZI

Allows tight engagement, prevents stripping



POZI SLOTTED COMBO

Found on 2-piece connectors

Use Pozi bit to drive

Use Pozi or Flat bit to remove



SQUARE

Popular in hand-driven applications

Allows tight engagement, prevents stripping



PHILLIPS SQUARE COMBO

Allows tight engagement, prevents stripping

Use Square or Combo bit to drive

Use Square, Combo, or Phillips bit to remove



HEX

Found on drivers and draw bolts

TYPE 17

