



Main

Product	Circuit Breaker Sub-Feed Lug
Provided equipment	Cover plate 1 Mounting plate 1 Bracket for support 2 Screw set 1 Connector 3 Rail extension 2 Rail splice 2 Terminal 3 Lug 1 Terminal shield 2
Circuit breaker type	H-frame

Complementary

Current Rating	250 A
Tightening torque	24.78...30.09 lbf.in (2.8...3.4 N.m)

Environment

Product certifications	CULus
------------------------	-------

Ordering and shipping details

Category	08338 - NF (& SHARED) RTI ACCESSORIES
Discount Schedule	PE1A
GTIN	00785901834717
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	Yes
Country of origin	US

Packing Units

Package 1 Height	2.30 in (5.842 cm)
Package 1 width	14.40 in (36.576 cm)
Package 1 Length	25.50 in (64.770 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------
