

# LC1D80008G7

IEC contactor, TeSys D, nonreversing, 125A  
resistive, 4 pole, 2 NO and 2 NC, 120VAC  
50/60Hz coil, open style, open style





## Main

|   |  |
|---|--|
| Range                                       | TeSys  |
| Product name                                | TeSys D  |
| Product or component type                   | Contacteur   |
| Device short name                           | LC1D   |
| Contacteur application                      | Resistive load   |
| Utilisation category                        | AC-1   |
| Poles description                           | 4P   |
| Power pole contact composition              | 2 NO + 2 NC  |
| [Ue] rated operational voltage              | Power circuit <= 300 V DC 25...400 Hz<br>Power circuit <= 690 V AC   |
| [Ie] rated operational current              | 125 A 140 °F (60 °C) <= 440 V AC AC-1 power circuit  |
| Control circuit type                        | AC 50/60 Hz  |
| [Uc] control circuit voltage                | 120 V AC 50/60 Hz  |
| [Uimp] rated impulse withstand voltage      | 8 kV IEC 60947   |
| Overvoltage category                        | III  |
| [Ith] conventional free air thermal current | 125 A 140 °F (60 °C) power circuit   |
| Irms rated making capacity                  | 1100 A 440 V power circuit IEC 60947   |
| Rated breaking capacity                     | 1100 A 440 V power circuit IEC 60947   |
| [Icw] rated short-time withstand current    | 640 A 104 °F (40 °C) - 10 s power circuit<br>990 A 104 °F (40 °C) - 1 s power circuit<br>135 A 104 °F (40 °C) - 10 min power circuit<br>320 A 104 °F (40 °C) - 1 min power circuit |
| Associated fuse rating                      | 200 A gG <= 690 V type 1 power circuit<br>160 A gG <= 690 V type 2 power circuit   |
| Average impedance                           | 0.8 mOhm - Ith 125 A 50 Hz power circuit   |
| [Ui] rated insulation voltage               | Power circuit 600 V CSA<br>Power circuit 600 V UL<br>Power circuit 1000 V IEC 60947-4-1  |
| Electrical durability                       | 0.8 Mcycles 125 A AC-1 <= 440 V  |
| Power dissipation per pole                  | 12.5 W AC-1  |
| Front cover                                 | Without  |
| Mounting support                            | Rail<br>Plate  |
| Standards                                   | CSA C22.2 No 14<br>EN 60947-4-1<br>EN 60947-5-1<br>IEC 60947-4-1<br>IEC 60947-5-1<br>UL 508  |
| Product certifications                      | CCC<br>RINA<br>CSA<br>BV<br>GOST<br>UL<br>GL<br>DNV<br>LROS (Lloyds register of shipping)  |

|                          |  |
|--------------------------|--|
| Connections - terminals  | Control circuit screw clamp terminals 2 0.00... 0.00 in <sup>2</sup> (1...2.5 mm <sup>2</sup> )flexible with cable end<br>Control circuit screw clamp terminals 1 0.00... 0.00 in <sup>2</sup> (1...2.5 mm <sup>2</sup> )flexible with cable end<br>Control circuit screw clamp terminals 1 0.00... 0.01 in <sup>2</sup> (1...4 mm <sup>2</sup> )flexible without cable end<br>Control circuit screw clamp terminals 2 0.00... 0.01 in <sup>2</sup> (1...4 mm <sup>2</sup> )flexible without cable end<br>Control circuit screw clamp terminals 1 0.00... 0.01 in <sup>2</sup> (1...4 mm <sup>2</sup> )solid without cable end<br>Control circuit screw clamp terminals 2 0.00... 0.01 in <sup>2</sup> (1...4 mm <sup>2</sup> )solid without cable end<br>Power circuit connector 1 0.01...0.08 in <sup>2</sup> (4... 50 mm <sup>2</sup> )flexible without cable end<br>Power circuit connector 2 0.01...0.04 in <sup>2</sup> (4... 25 mm <sup>2</sup> )flexible without cable end<br>Power circuit connector 1 0.01...0.08 in <sup>2</sup> (4... 50 mm <sup>2</sup> )flexible with cable end<br>Power circuit connector 2 0.01...0.02 in <sup>2</sup> (4... 16 mm <sup>2</sup> )flexible with cable end<br>Power circuit connector 1 0.01...0.08 in <sup>2</sup> (4... 50 mm <sup>2</sup> )solid without cable end<br>Power circuit connector 2 0.01...0.04 in <sup>2</sup> (4... 25 mm <sup>2</sup> )solid without cable end |
| Tightening torque        | Control circuit 10.62 lbf.in (1.2 N.m) screw clamp terminals flat Ø 6 mm<br>Control circuit 10.62 lbf.in (1.2 N.m) screw clamp terminals Philips No 2<br>Power circuit 106.21 lbf.in (12 N.m) connector flat Ø 6 to Ø 8 mm<br>Power circuit 106.21 lbf.in (12 N.m) connector hexagonal 0.16 in (4 mm)  |
| Operating time           | 20...35 ms closing<br>6...20 ms opening  |
| Safety reliability level | B10d = 1369863 cycles contactor with nominal load EN/ISO 13849-1<br>B10d = 20000000 cycles contactor with mechanical load EN/ISO 13849-1   |
| Mechanical durability    | 4 Mcycles  |
| Maximum operating rate   | 3600 cyc/h 140 °F (60 °C)  |

## Complementary

|                                 |   |
|---------------------------------|---|
| Coil technology                 | Without built-in suppressor module  |
| Control circuit voltage limits  | 0.85...1.1 Uc -40...131 °F (-40...55 °C) operational AC 60 Hz<br>0.3...0.6 Uc -40...158 °F (-40...70 °C) drop-out AC 50/60 Hz<br>0.8...1.1 Uc -40...131 °F (-40...55 °C) operational AC 50 Hz<br>1...1.1 Uc 131...158 °F (55...70 °C) operational AC 50/60 Hz |
| Inrush power in VA              | 245 VA 60 Hz 0.75 68 °F (20 °C))<br>245 VA 50 Hz 0.75 68 °F (20 °C))  |
| Hold-in power consumption in VA | 26 VA 60 Hz 0.3 68 °F (20 °C))<br>26 VA 50 Hz 0.3 68 °F (20 °C))  |
| Heat dissipation                | 6...10 W 50/60 Hz   |

## Environment

|                                       |   |
|---------------------------------------|---|
| IP degree of protection               | IP20 front face IEC 60529   |
| Protective treatment                  | TH IEC 60068-2-30   |
| Pollution degree                      | 3   |
| Ambient air temperature for operation | -40...140 °F (-40...60 °C)<br>140...158 °F (60...70 °C) with derating   |
| Ambient air temperature for storage   | -76...176 °F (-60...80 °C)  |
| Operating altitude                    | 0...9842.52 ft (0...3000 m)   |
| Fire resistance                       | 1562 °F (850 °C) IEC 60695-2-1  |
| Flame retardance                      | V1 conforming to UL 94  |
| Mechanical robustness                 | Vibrations contactor open 2 Gn, 5...300 Hz<br>Shocks contactor open 8 Gn for 11 ms<br>Vibrations contactor closed: 3 Gn, 5...300 Hz<br>Shocks contactor closed: 10 Gn for 11 ms |
| Height                                | 5.00 in (127 mm)  |

|            |                       |
|------------|-----------------------|
| Width      | 3.78 in (96 mm)       |
| Depth      | 5.51 in (140 mm)      |
| Net Weight | 4.06 lb(US) (1.84 kg) |

### Ordering and shipping details

|                       |   |
|-----------------------|---|
| Category              | 22359 - CTR, TESYS D, OPEN, 80-150A AC&DC |
| Discount Schedule     | I12                                       |
| GTIN                  | 00785901474524                            |
| Nbr. of units in pkg. | 1   |
| Package weight(Lbs)   | 3.93 lb(US) (1.78 kg)                     |
| Returnability         | Yes                                       |
| Country of origin     | CZ  |

### Packing Units

|                        |                   |
|------------------------|-------------------|
| Unit Type of Package 1 | PCE               |
| Package 1 Height       | 4.33 in (11 cm)   |
| Package 1 width        | 5.31 in (13.5 cm) |
| Package 1 Length       | 6.10 in (15.5 cm) |

### Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product   |
| California proposition 65  | WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH Regulation           | <a href="#">REACH Declaration</a>   |
| REACH free of SVHC         | Yes   |
| EU RoHS Directive          | Compliant <a href="#">EU RoHS Declaration</a>   |
| Toxic heavy metal free     | Yes   |
| Mercury free               | Yes   |
| RoHS exemption information | <a href="#">Yes</a>   |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>  |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>   |
| WEEE                       | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.  |
| PVC free                   | Yes   |

### Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|