



Main

| | |
|-----------------------------|---|
| Range | Spacial |
| Product name | Spacial SM |
| Product or component type | Compact enclosure |
| Application | Multi-purpose |
| Installation accessory type | Floor-standing |
| Device composition | 1 body 2 door 2 cable gland plate 1 locking system with handle door 1 blocking system left door 4 mounting plate bracket 1 mounting plate |
| Removable parts | Door by screws hinge Mounting plate by screws mounting plate bracket Mounting plate bracket by screws |
| Enclosure nominal height | 70.87 in (1800 mm) |
| Enclosure nominal width | 47.24 in (1200 mm) |
| Enclosure nominal depth | 19.69 in (500 mm) |

Complementary

| | |
|-----------------------------|--|
| Number of doors | Front 2 |
| Door opening side | Left 120 °) Right 120 °) |
| Door type | Solid |
| Lock type | 4 points lock, handle with 5 mm double bar insert |
| Body type | Front part forming a rigid frame with welded corners Single piece body with welded rear panel |
| Mounting plate description | Plain |
| Type of gland plate | Standard |
| Cable entry | 1 entry |
| Material | Mounting plate galvanised steel Body sheet steel Door sheet steel Hinge zamak |
| Surface finish | Epoxy-polyester powder |
| Color | Enclosure Gray RAL 7035) Handle Black RAL 9005) |
| Accessibility for operation | Front |
| Net Weight | 359.35 lb(US) (163 kg) |

Environment

| | |
|-------------------------|------------------------------|
| Standards | IEC 62208 |
| Product certifications | DNV UL BV |
| IK degree of protection | IK10 conforming to IEC 62262 |
| IP degree of protection | IP55 conforming to IEC 60529 |

Ordering and shipping details

| | |
|-----------------------|---------------------------------------|
| Category | 80035 - ENCLOSURE SYSTEMS FLOOR MOUNT |
| Discount Schedule | ES1 |
| GTIN | 00785901504474 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 358.6 lb(US) (162.66 kg) |
| Returnability | No |
| Country of origin | ES |

Packing Units

| | |
|------------------|------------------------|
| Package 1 Height | 75.98 in (1930.000 mm) |
| Package 1 width | 49.02 in (1245.000 mm) |
| Package 1 Length | 23.23 in (590.000 mm) |

Offer Sustainability

| | |
|----------------------------|--|
| Sustainable offer status | Green Premium product |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|