


Product data sheet

Characteristics

QO154L225PQG

Load center, QO, 1 phase, 54 spaces, 64 circuits, 225A convertible main lugs, PoN, NEMA1, Qwik-grip, gnd bar, UL



Main

Marketing Trade Name	QO
Product Type	Load Center
Provided Equipment	Qwik grip assembly kit 1)

Complementary

Tightening Torque	Main lugs 250 lb.in, AWG 4...250 kcmil, aluminium/copper
Load Center Type	Main lugs
Rated Current	225 A
Number of Spaces	54
Maximum Number of Single Pole Circuits	64
Maximum Number of Tandem Breakers	10
Number of Phases	1 phase
Ground Bar	Grounding bar included (not installed)
Height	39.37 in (1000 mm)
Width	14.25 in (362 mm)
Depth	3.74 in (95 mm)

Environment

Enclosure Rating	NEMA 1 indoor
Ambient Air Temperature for Operation	23 °F (-5 °C) 104 °F (40 °C)
Product Certifications	UL Listed

Ordering and shipping details

Category	10003 - QO PON 1PH LC,12-60 CKT, ML N1
Discount Schedule	DE3A
GTIN	00785901886617
Nbr. of units in pkg.	1
Package weight(Lbs)	22 lb(US) (9.98 kg)
Returnability	Yes
Country of origin	US

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration