

Garant**WNMG 060408, Grade: HB7010-1**

Order data

Order number	252064 HB7010-1
GTIN	4045197780324
Item class	21G

Description

WN.G 060408 HB7010-1 Grade: HB7010-1
Chip breaker: SM
Tolerance: M
Cutting depth a_p : 0.5 - 4 mm
Feed f : 0.2 - 0.5 mm/rev.
Cutting speed v_c main application: 120 - 440 m/min

Technical description

Feed f	0.2 - 0.5 mm/rev.
Cutting speed v_c main application	120 - 440 m/min
Chip breaker	SM
Cutting depth a_p	0.5 - 4 mm
Main application	P
Cutting conditions	continuous
Grade	HB7010-1

Corner radius	0.8 mm
Finishing/roughing assignment	Semi-roughing
Tool material	Carbide
ISO code indexable insert	WNMG 060408
Number of changes/inserts	6
Tolerance	M
Type of product	Indexable insert for turning