



NOTE:

1. MATERIAL:
 1008-1010 CRCQ Steel (Unit is based upon pound)

Typical Rb range - 45-65
 Typical Yield- 30,000-33,000
 Typical Tensile 42,000-45,000
 Typical Elongation: 35%

2. PACKAGED:
 100 PCS/Inner box
 400 PCS/Carton

REV: C	10/31/01
REV: B	09/13/01
REV: A	07/31/01

DRAWN BY: John Lai	SCALE: 1/1	DATE: 8/22/00
-----------------------	---------------	------------------

UNLESS OTHERWISE SPECIFIED
 DIMENSIONS AND TOLERANCING
 ARE IN MILLIMETERS (INCHES)

TOLERANCES

.X ± .1
 .XX ± .03
 .XXX ± .005

HARDWARE RESOURCES

4319 MARLENA ST, BOSSIER CITY, LA 71111

MATERIAL: 1008-1010 CRCQ Steel

PART NAME:

ITEM NO: 33530

PLATING: PB