

Garant**WNMG 080408, Grade: HB7010-1**

Order data

Order number	252208 HB7010-1
GTIN	4045197780362
Item class	21G

Description

WNMG 080408 HB7010-1 Grade: HB7010-1

Chip breaker: SG

Cutting depth a_p : 1.5 - 6 mmFeed f : 0.25 - 0.6 mm/rev.Cutting speed v_c main application: 100 - 375 m/min

Technical description

Cutting depth a_p	1.5 - 6 mm
Corner radius	0.8 mm
Cutting speed v_c main application	100 - 375 m/min
Main application	P
Grade	HB7010-1
Feed f	0.25 - 0.6 mm/rev.
Chip breaker	SG
Cutting conditions	continuous

Finishing/roughing assignment	Roughing
Tool material	Carbide
ISO code indexable insert	WNMG 080408
Number of changes/inserts	6
Type of product	Indexable insert for turning