# HOLEX

### Solid carbide slot drill, uncoated, Ø e8 DC: 20 mm



## Order data

Order number	202241 20
GTIN	4045197767080
Item class	12X

## Description

#### Version:

**Eccentric relief ground**, additionally **finish ground** in the flutes for **outstanding chip evacuation** in long-chipping aluminium workpieces.

#### **Application:**

For roughing and finishing. Through-coolant: no Tolerance nominal  $\emptyset$ : e8 No. of teeth Z: 3 Helix angle: 45 degrees Direction of infeed: horizontal, oblique and vertical Shank: DIN 6535 HA to h6 No. of teeth Z: 3 Flute length L<sub>c</sub>: 40 mm Overall length L: 104 mm Shank  $\emptyset$  D<sub>s</sub>: 20 mm Feed f<sub>z</sub> for slot milling in short-chipping aluminium: 0.085 mm Feed f<sub>z</sub> for side milling in short-chipping aluminium: 0.12 mm

# **Technical description**

Feed $f_z$ for slot milling in short-chipping aluminium	0.085 mm
Direction of infeed	horizontal, oblique and vertical
Feed $f_z$ for side milling in short-chipping aluminium	0.12 mm
No. of teeth Z	3
Flute length $L_c$	40 mm

© Hoffmann GmbH Qualitätswerkzeuge

Shank Ø D <sub>s</sub>	20 mm
Shank	DIN 6535 HA to h6
Overall length L	104 mm
Cutting edge $Ø D_c$	20 mm
Tolerance nominal Ø	e8
Helix angle	45 degrees
Corner chamfer angle	90 degrees
Coating	uncoated
Tool material	Solid carbide
Standard	Manufacturer's standard
Туре	W
Cutting width $a_e$ for milling operation	0.5×D for side milling
Cutting width $a_e$ for milling operation	Full slot cutting depth 1×D
Through-coolant	no
Colour ring	yellow
Type of product	End mill

# Services

Shank clamping flats for shrink-fit chucks, with retainer function Shank Ø tool 20 mm	SZ2025 20
Shank grinding Type HB	129100 HB