

Garant
Die, UNF: 7/16-20


Order data

Order number	142620 7/16-20
GTIN	4045197084934
Item class	11K

Description

Version:

Closed, pre-slit form; **with tapered lead chamfer on both sides** for easy start to the threading action and clean swarf evacuation in the direction of cutting. **1¾ turns lead chamfer.**

Application:

For UNF uniform fine threads ASME – B1.1.

Tolerance class: 2A

Threads per inch: 20

Thread Ø: 11.11 mm

External Ø: 30 mm

Height: 11 mm

Technical description

Height	11 mm
Thread Ø	11.11 mm
Threads per inch	20
External Ø	30 mm

Thread size	7/16-20 UNF
Cutting direction	right-hand
Thread type	UNF
Flank angle	60 °
Tool material	HSS
Standard	EN 22568
Tolerance class	2A
Type of product	Die

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions		
Steel < 500 N/mm ²	suitable		
Steel < 750 N/mm ²	suitable		
Oil	suitable		
dry	suitable only under restricted conditions		