

**Garant**
**High-precision countersink 90°, uncoated, External Ø Dc: 11,5mm**

**Order data**

Order number	150150 11,5
GTIN	4045197085504
Item class	11M

**Description**
**Version:**

**All countersinks have 3 cutting edges**, radially relieved.

Flutes are ground from solid.

High-precision countersink, produced with tight manufacturing tolerances similar to DIN 335-C.

**Application:**

High precision countersinks for chatter-free countersinking.

Through-coolant: no

Number of cutting edges Z: 3

Number of cutting edges Z: 3

smallest countersink Ø for holes from: 2.8 mm

Overall length L: 56 mm

Shank Ø D<sub>s</sub>: 8 mm

for countersunk screws ISO 2009, 2010, 7046, 7047: M6

Feed f in steel < 500 N/mm<sup>2</sup>: 0.12 mm/rev.

**Technical description**

Feed f in steel < 500 N/mm <sup>2</sup>	0.12 mm/rev.
Shank tolerance	h9
for countersunk screws ISO 2009, 2010, 7046, 7047	M6
External Ø	11.5 mm
smallest countersink Ø for holes from	2.8 mm
Shank Ø D <sub>s</sub>	8 mm

Overall length L	56 mm
Number of cutting edges Z	3
Coating	uncoated
Countersink tip angle	90 °
Tool material	HSS
Standard	DIN 335 C
Shank	Plain shank with h9
Through-coolant	no
Colour ring	without
Type of product	Stepped drill and countersink

## User data

	Suitability	V <sub>c</sub>	ISO code
Alu plastics	suitable	70 m/min	N
Aluminium (short chipping)	suitable	33 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	28 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	27 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable only under restricted conditions	27 m/min	P
wet maximum	suitable		
dry	suitable only under restricted conditions		