

Garant**Die, UNC: 6-32**

Order data

Order number	142520 6-32
GTIN	4045197084750
Item class	11K

Description

Version:

Closed, pre-slit form; **with tapered lead chamfer on both sides** for easy start to the threading action and clean swarf evacuation in the direction of cutting. **1¾ turns lead chamfer.**

Application:

For UNC uniform coarse threads ASME – B1.1.

Tolerance class: 2A

Threads per inch: 32

Thread Ø: 3.51 mm

External Ø: 20 mm

Height: 7 mm

Technical description

Thread Ø	3.51 mm
Height	7 mm
Threads per inch	32
External Ø	20 mm

Cutting direction	right-hand
Thread type	UNC
Flank angle	60 °
Tool material	HSS
Standard	EN 22568
Tolerance class	2A
Type of product	Die

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions		
Steel < 500 N/mm ²	suitable		
Steel < 750 N/mm ²	suitable		
Oil	suitable		
dry	suitable only under restricted conditions		