

**Garant**
**Toolholder with ratchet long, All-steel, Overall length: 250mm**

**Order data**

Order number	149001 250
GTIN	4062406754686
Item class	11K

**Description**
**Version:**

With two-jaw chuck for clamping square shanks. Moveable T-handle with a groove centred at each end for engaging the retaining ball. **Holder with stainless steel sheath**. Ratchet is reversible and can also be locked. **All-steel construction** for high torque applications. Clamping jaws milled and hardened for high toughness and optimum surface hardness.

**Application:**

Suitable for tapping holes where access is difficult.

**Note:**

The square sizes of other tap and reamer sizes can be found in the tables in the respective Product Groups.

Capacity □: 2.5 - 5.5 mm

for hand taps DIN 352: M3 – M10

Spare jaws No. 148712 size: 85

**Technical description**

for hand taps DIN 352	M3 – M10
Capacity □	2.5 - 5.5 mm

Overall length	250 mm
Spare jaws No. 148712 size	85
Material	All-steel
Type of product	Pin vice