

Magnetic retriever flexible, Magnet tensile force: 500g



Order data

Order number	081670 500
GTIN	4045197487117
Item class	02A

Description

Version:

With permanent magnet. Flexible chrome-plated shank with permanent magnet, 2-component plastic handle.

Function:

IP20: No protection against penetration by foreign bodies with \emptyset < 12 mm, however touching should be avoided, and no protection against water.

External Ø: 8 mm Overall length: 520 mm Magnet Ø: 6 mm

Magnet retaining force: 5 N

Technical description

Magnet retaining force	5 N
Magnet tensile force	500 g
Overall length	520 mm
Magnet Ø	6 mm
External Ø	8 mm
Type of product	Magnetic retrievers