

Garant**CNMG 120408, Grade: HB7120-1**

Order data

Order number	250060 HB7120-1
GTIN	4045197819581
Item class	21G

Description

CNMG 120408 HB7120-1 Grade: HB7120-1
Chip breaker: VS
Cutting depth a_p : 0.3 - 2.5 mm
Feed f : 0.15 - 0.5 mm/rev.
Cutting speed v_c main application: 90 - 290 m/min

Technical description

Feed f	0.15 - 0.5 mm/rev.
Chip breaker	VS
Main application	M
Grade	HB7120-1
Corner radius	0.8 mm
Cutting conditions	continuous
Cutting speed v_c main application	90 - 290 m/min

Cutting depth a_p	0.3 - 2.5 mm
Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	CNMG 120408
Number of changes/inserts	4
Type of product	Indexable insert for turning