



HOLEX Pro Steel solid carbide drill, plain shank DIN 6535 HA, TiAlN, Ø DC h7 (mm or inch): 18



Order data

Order number	122501 18
GTIN	4045197825353
Item class	12F

Description

Version:

Straight major cutting edges and a **special flute profile** ensure a good chip evacuation. The robust cutter geometry ensures high-performance drilling with good process reliability.

A wide range of applications in steel materials thanks to a combination of tough ultra-fine grain carbide and an extremely wear-resistant coating.

Up to Ø 1.9 with 4 facets, from Ø 2 with relieved cone.

Cutting chisel edge with **high centring accuracy** due to **strong core and special point geometry**. **Straight major cutting edges** with slightly honed edges and special flute profile produce **short chips**.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

Versions with HB and HE shank available at the same price as HA.

For **HB shanks**: use order **no. 122502**.

For **HE shanks**: use order **No. 122503**.

Standard: DIN 6537 K

Tolerance nominal Ø: h7

Number of cutting edges Z: 2

Tolerance nominal Ø: h7

recommended maximum drilling depth L_2 : 46 mm

Overall length L: 123 mm

Shank Ø D_s : 18 mm

Feed f in steel < 900 N/mm²: 0.28 mm/rev.

Technical description

Number of cutting edges Z	2
---------------------------	---

recommended maximum drilling depth L_2	46 mm
Tolerance nominal \varnothing	h7
Flute length L_c	73 mm
Overall length L	123 mm
Feed f in steel $< 900 \text{ N/mm}^2$	0.28 mm/rev.
Nominal $\varnothing D_c$	18 mm
Shank $\varnothing D_s$	18 mm
Standard	DIN 6537 K
Series	Pro Steel
Coating	TiAlN
Tool material	Solid carbide
Version	4xD
Point angle	140°
Shank	DIN 6535 HA to h6
Through-coolant	no
Machining strategy	HPC
Semi-Standard	yes
Colour ring	green
Type of product	Jobber drill

User data

	Suitability	V_c	ISO code
Steel $< 500 \text{ N/mm}^2$	suitable	115 m/min	P
Steel $< 750 \text{ N/mm}^2$	suitable	105 m/min	P
Steel $< 900 \text{ N/mm}^2$	suitable	85 m/min	P
Steel $< 1100 \text{ N/mm}^2$	suitable	80 m/min	P
Steel $< 1400 \text{ N/mm}^2$	suitable	60 m/min	P
INOX $< 900 \text{ N/mm}^2$	suitable	30 m/min	M

INOX > 900 N/mm ²	suitable only under restricted conditions	25 m/min	M
GG	suitable	90 m/min	K
GGG	suitable	55 m/min	K
Uni	suitable		
wet maximum	suitable		
dry	suitable		