

**Magnetic retriever flexible, Magnet tensile force: 300g****Order data**

Order number	081670 300
GTIN	4045197487100
Item class	02A

Description**Version:**

With permanent magnet. Flexible chrome-plated shank with permanent magnet, 2-component plastic handle.

Function:

IP20: No protection against penetration by foreign bodies with $\varnothing < 12$ mm, however touching should be avoided, and no protection against water.

External \varnothing : 7.5 mm

Overall length: 520 mm

Magnet \varnothing : 5 mm

Magnet retaining force: 3 N

Technical description

Magnet retaining force	3 N
Overall length	520 mm
Magnet \varnothing	5 mm
Magnet tensile force	300 g
External \varnothing	7.5 mm
Type of product	Magnetic retrievers