


**Abrasive sleeve holder, slit, shank \varnothing 6 mm, Head \varnothing ×head length: 22X20 mm****Order data**

Order number	553600 22X20
GTIN	4045197240187
Item class	52E

Description**Version:**

Slotted, resilient rubber body with steel shank. Ground outer face for best concentricity.

minimum speed: 18000 rpm

maximum speed: 26000 rpm

Technical description

maximum speed	26000 rpm
minimum speed	18000 rpm
Head \varnothing	22 mm
Head length	20 mm
Shape description	cylindrical
Shank \varnothing	6 mm
Backing material	resilient rubber body