


Garant
CNMG 120408, Grade: HB7035-1


Order data

Order number	250060 HB7035-1
GTIN	4045197873866
Item class	21G

Description

CNMG 120408 HB7035-1 Grade: HB7035-1
 Chip breaker: SS
 Cutting depth a_p : 0.3 - 2.5 mm
 Feed f : 0.1 - 0.4 mm/rev.
 Cutting speed v_c main application: 120 - 350 m/min

Technical description

Cutting depth a_p	0.3 - 2.5 mm
Main application	P
Chip breaker	SS
Grade	HB7035-1
Feed f	0.1 - 0.4 mm/rev.
Corner radius	0.8 mm
Cutting conditions	heavily interrupted

Cutting speed v_c main application	120 - 350 m/min
Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	CNMG 120408
Number of changes/inserts	4
Type of product	Indexable insert for turning