


Garant**WNMG 080408, Grade: HB7035-1**

Order data

Order number	252070 HB7035-1
GTIN	4045197875044
Item class	21G

Description

WN.G 080408 HB7035-1 Grade: HB7035-1

Chip breaker: SM

Tolerance: M

Cutting depth a_p : 0.5 - 4 mmFeed f : 0.2 - 0.5 mm/rev.Cutting speed v_c main application: 100 - 320 m/min

Technical description

Cutting speed v_c main application	100 - 320 m/min
Corner radius	0.8 mm
Grade	HB7035-1
Chip breaker	SM
Cutting conditions	heavily interrupted
Cutting depth a_p	0.5 - 4 mm
Feed f	0.2 - 0.5 mm/rev.

Main application	P
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
ISO code indexable insert	WNMG 080408
Number of changes/inserts	6
Tolerance	M
Type of product	Indexable insert for turning