

## Garant

**Circular saw blade, wood, alternating teeth medium, Blade Ø D: 300mm**



### Order data

Order number	584035 300
GTIN	4045197220776
Item class	51S

### Description

#### Version:

**Tipped with carbide inserts**, precision version with high-strength blade, noise damped. Generously dimensioned carbide teeth allow multiple re-grinding.

#### Application:

For circular, cross-cut, compound, and mitre saws.

Type UW for **board materials, veneered or plastic coated on one side**, veneer packs longitudinally, hard paper and hard fabric.

#### Note:

**Further circular saw blades can be found in Group 17.**

Bore Ø: 30 mm

Drive holes number/Ø/pitch circle: 2/7/42 and 2/9/46 and 2/10/60 mm

Number of teeth: 48

Width of cut B: 3.2 mm

### Technical description

Bore Ø	30 mm
Blade Ø D	300 mm

Number of teeth	48
Width of cut B	3.2 mm
Drive holes number/Ø/pitch circle	2/7/42 and 2/9/46 and 2/10/60 mm
Type of product	Circular saw blade