

Garant
Open ended spanner / ratchet ring spanner, Width across flats: 9mm

Order data

Order number	614800 9
GTIN	4045197160195
Item class	61B

Description
Version:

Drop forged. Ring end with especially smooth–running reversible ring ratchet. Extremely small working arc of 5°.

Material:

Chrome vanadium steel, matt chrome-plated.

Spanner length L: 143 mm

Jaw width b: 19.3 mm

Jaw height h_1 : 5 mm

Ring thickness h_2 : 7.6 mm

Ring \varnothing D: 19 mm

Ratchet torque rating: 40 N·m

Technical description

Ring thickness h_2	7.6 mm
Spanner length L	143 mm
Width across flats	9 mm
Jaw height h_1	5 mm
Ring \varnothing D	19 mm
Ratchet torque rating	40 N·m
Jaw width b	19.3 mm
Width across flats	metric
Ring setting	0°

No. of teeth	72
Working arc	5 °
Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	matt chrome-plated
Type of product	Spanner